





LOC	DIST	REVISIONS					
P	LTR	DESCRIPTION			DATE	DWN	APVD
	A	REVISED PER ECO-09-014471			18JUN09	HMR	CR



CLAMPING SCREW



WIRE ENTRY




MATING FACE

MATERIALS AND FINISH:
HOUSING: PA 6-6, UL94V-0, COLOR: GREEN.
CLAMP: BRASS, NICKEL PLATED.
CONTACT SPRING: PHOSPHOR BRONZE, TIN PLATED.
CLAMPING SCREW: M2, BRASS, NICKEL PLATED.

ELECTRICAL:
VOLTAGE RATING: 300V
CURRENT RATING: 11A
WIRE SIZE RANGE: 14-30 AWG

ENVIRONMENTAL:
OPERATING TEMP RANGE: -40°C TO +110°C

56.0	16	1-1986371-6
52.5	15	1-1986371-5
49.0	14	1-1986371-4
45.5	13	1-1986371-3
42.0	12	1-1986371-2
38.5	11	1-1986371-1
35.0	10	1-1986371-0
31.5	9	1986371-9
28.0	8	1986371-8
24.5	7	1986371-7
21.0	6	1986371-6
17.5	5	1986371-5
14.0	4	1986371-4
10.5	3	1986371-3
7.0	2	1986371-2
DIM L	NO OF POS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLEGEL 18MAR2008		 Tyco Electronics Corporation Harrisburg, PA 17105-3608						
DIMENSIONS: mm		CHK C RICHARD 3/19/08		NAME TERMINAL BLOCK, PLUG, VERTICAL STACKING LEFT HAND, 3.50mm PITCH						
		APVD C RICHARD 3/19/08								
		PRODUCT SPEC —								
		APPLICATION SPEC —								
TOLERANCES UNLESS OTHERWISE SPECIFIED:		WEIGHT —		SIZE A3	CAGE CODE 00779	DRAWING NO C-1986371	RESTRICTED TO —			
0 PLC ± — 1 PLC ± 0.3 2 PLC ± 0.25 3 PLC ± — 4 PLC ± — ANGLES ± 2°		MATERIAL —		FINISH —		CUSTOMER DRAWING		SCALE NTS	SHEET 1 OF 1	REV A