




△ 7287-0178-40 (CODE B)



SUB ASSEMBLY PART NO. AND CH. CODE		PART NO. AND CH. CODE	PART NAME		MATERIAL	COLOR	QTY.
△ 7283-8852-30. [D]	①	7183-8852-30	△ RH TYPE 3P HOUSING		PBT	BLACK	1
	②	7158-5264	△ RH TYPE 3P FRONT HOLDER		PBT	△ NATURAL	1
	③	7137-2814-80	△ RH TYPE 3P PACKING		SILICONE RUBBER	BROWN	1
	④	7187-0178-40	△ RH TYPE 3P HOUSING		PBT	LIGHT GRAY	1
	②	7158-5264	△ RH TYPE 3P FRONT HOLDER		PBT	NATURAL	1
△ 7287-0178-40		③	△ RH TYPE 3P PACKING		SILICONE RUBBER	BROWN	1

注記

- △ 1. かん合相手品番 : 7282-8852-30 (CODE A のみ)
2. 適用端子品番 : 7116-4415-02 ETC.
3. 適用コネクタ品番 : 7158-3165-90, 7158-3166-60, 7158-3167-80
7158-3168-80
4. 適用防水栓品番 : 7158-3169-40

NOTES

- △ 1. MATING PART NO. : 7282-8852-30 (CODE A ONLY)
2. APPLICABLE TERMINAL NO. : 7116-4415-02 ETC.
3. APPLICABLE SEAL RUBBER NO. : 7158-3165-90, 7158-3166-60, 7158-3167-80
7158-3168-80
4. APPLICABLE UNUSED CAVITY PLUG: 7158-3169-40

△ 6	2011/01/26	CHANGED PART NAME, ETC.	C11-Z051	Y. F
△ 5	2006/11/28	ADDED PART NO., ETC., [D]	C06-ZD06	Y. I
△ 4	05/01/07	CHANGED FORM. [C]	C04-ZF72	T. Y
△ 3	03/08/07	CHANGED CODE. [B]	C03-X324	T. Y
△ 2	02/05/17	CHANGED FORM. [A]	C02-X538	T. Y
△ 1	02/02/06	ELIMINATE SECTION	C02-X199	T. Y
LET	01/11/08	NEW	C01-Y135	T. Y
DATE		REVISION RECORD	NO.	CHKD

GENERAL TOLERANCE

	10MAX	50MAX	100MAX	250MAX	2500R	ANGLE	EGGENT
A	±0.15	±0.2	±0.3	±0.5	±0.75	±30°	O. 1
B	±0.2	±0.3	±0.55	±0.95	±1.4	±30°	O. 1
△ C	±0.3	±0.5	±0.8	±1.4	±2	±30°	O. 15

SPECIFIED

CUSTOMER		CUSTOMER PART NO.	
OFFICE		TRIAL PART NO.	
VENDOR			
VENDOR NO.			
DWG TYPE	DWG SOURCE	DWG DATE	UNIT
R	NEW	01/11/08	mm
APPROVED	CHECKED	CHECKED	DESIGN

M. KASHIYAMA	Y. FUKASE	M. KASHIYAMA	R. EVANGELISTA
2011/01/26		2011/01/26	01/05/08

MATERIAL SPEC.		TREAT. & FIN.	
NAME			
△ RH TYPE 3P HOUSING			
FEMALE SUB ASSEMBLY			

PART NO.	CH. CODE	PART NO.	CH. CODE
△ 7283-8852-30 ETC.		△ 7283-8852-30 : R	
7283-8852-30 : R		SET DWG NO.	

YAZAKI CORPORATION

ISSUE MARK