



SEC. A-A



SEC. B-B

△ PART NO. AND CH. CODE	△ COLOR
7122-3010	NATURAL
7122-3010-30	BLACK
7122-3010-40	LIGHT GRAY
7122-3010-60	GREEN

△ 注 記

1. かん合相手品番 : 7123-3010

2. 適用端子品番 : 7114-3030

△ NOTES

1. MATING PART NO. : 7123-3010

2. APPLICABLE TERMINAL NO. : 7114-3030

△	11. 01. 14	CHANGED PART NAME	C11-ZA30	C. S
△	10. 03. 11	DELETED VIEWS, ETC.	C10-Z157	T. O
△	98. 10. 29	ADDED COLOR NO. & NOTES	C98-M813	T. M
△	97. 06. 20	CHANGED DIMENSION & CAD DRAWN	C97-M243	M. T
△	88. 11. 28	色番追加	8MC-1638	山 本
△	75. 05. 20	材質変更	C5-273	かわの
△	74. 10. 12	部番追加及び材質変更 差換図作成	C4-713	渡 辺
LET	DATE	REVISION RECORD	NO.	CHKD

GENERAL TOLERANCE							
	10MAX	50MAX	100MAX	250MAX	2500VR	ANGLE	ECCENT
A	±0. 15	±0. 2	±0. 3	±0. 5	±0. 75	±30'	0. 1
B	±0. 2	±0. 3	±0. 55	±0. 95	±1. 4	±30'	0. 1
◎	±0. 3	±0. 5	±0. 8	±1. 4	±2	±30'	0. 15
SPECIFIED						MASS	

CUSTOMER							
CUSTOMER PART NO.				CUSTOMER DWG NO.			
OFFICE				TRIAL PART NO.			
VENDOR				-----			
VENDOR NO.				-----			
DWG TYPE	DWG SOURCE			DWG DATE	UNIT	SCL	ANGL
R	NEW			69. 08. 05	mm	2:1	3
APPROVED	CHECKED	CHECKED	DESIGN	DRAWN			
S. MIZUSE	-----	R. DE GUZMAN	K. KIMURA	C. SANJOAQUIN			
11. 01. 14	-----	11. 01. 14		11. 01. 14			

MATL. <u>△</u> PA66 (SEE TABLE)		TREAT. & FIN.	
NAME <u>△</u> 1P HOUSING MALE			
PART NO. CH. CODE		7122-3010 ETC.	
DWG NO.		7122-3010 :R	SET DWG NO.
YAZAKI CORPORATION			

YAZAKI CORPORATION

ISSUE MARK