


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	ECO-20-004897	24AUG2020	SB	JB


D

D




C

C



B

B



A

A




FIG 1

- FOR ADDITIONAL SPECIFICATIONS SEE AMP PRODUCT SPEC 108-7532.
- SWITCH SHOWN IN OPEN POSITION.
- ALL CHARACTERS AND ROCKERS ARE WHITE, HOUSING IS BLUE.
- LASER MARKING WILL VARY ON 2 AND 3 POSITION SIDES DUE TO SPACE RESTRICTIONS.
- .315 DIMENSION APPLIES AT TERMINAL TIPS. TERMINALS ARE .300 +.010 AT MOUNTING SURFACE. -.000
- ALL MATERIALS AND FINISHES SHALL COMPLY WITH EU DIRECTIVE 2002 /95/EC OF 27JAN2003 (ROHS).
- MATERIAL: HOUSING AND ROCKERS - POLYESTER CONTACT & SOLDER LEAD - COPPER ALLOY
- FINISH: CONTACT - GOLD OVER NICKEL SOLDER LEAD - TIN OVER NICKEL
- OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- MARKS WILL BE ADDED BY LASER MARK PROCESS.

9	OBSOLETE	FIG 7	—	.58	5	8-5435668-7
		FIG 2	FIG 1	.58	5	3-5435668-5
				.48	4	3-5435668-4
				.38	3	3-5435668-3
9	OBSOLETE			1.28	12	3-5435668-2
9	OBSOLETE			1.18	11	3-5435668-1
				1.08	10	3-5435668-0
9	OBSOLETE			.98	9	2-5435668-9
				.88	8	2-5435668-8
				.78	7	2-5435668-7
				.28	2	2-5435668-6
			.68	6	2-5435668-5	
			—	1.08	10	5435668-9
			—	.88	8	5435668-7
			—	.68	6	5435668-5
			—	.58	5	5435668-4
		—	.48	4	5435668-3	
9	OBSOLETE		—	.28	2	5435668-1
		MARKING	SEALING TAPE	A	NO OF POSN	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN BSV	08JAN05	TE Connectivity Ltd.		
		CHK	-			
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD	-	NAME		
	0 PLC ± -	PRODUCT SPEC	-	SWITCH ASSY, DIP, TYPE C, 7100 SERIES, SPST, LOW PROFILE		
	1 PLC ± -	-	-			
	2 PLC ± -	APPLICATION SPEC	-			
	3 PLC ± .005	-	-			
MATERIAL	4 PLC ± -	WEIGHT	-	SIZE	CAGE CODE	DRAWING NO
7	ANGLES ± ± -	-	-	A2	00779	C=5435668
		FINISH	8	SCALE	4:1	SHEET 1 of 2
		CUSTOMER DRAWING	-	REV	B	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—




FIG 2




FIG 7

D

D

C

C


B

5435668

B

A

A

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN BSV		08JAN05		 TE Connectivity Ltd.											
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± .005 4 PLC ± — ANGLES ± —		CHK —		NAME SWITCH ASSY, DIP, TYPE C, 7100 SERIES, SPST, LOW PROFILE											
				APVD —													
PRODUCT SPEC —																	
APPLICATION SPEC —																	
				SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO							
MATERIAL —		FINISH —		WEIGHT —		A2		00779		C=5435668		—					
CUSTOMER DRAWING						SCALE		4:1		SHEET		2 of 2		REV		B	