

OP-AR16([Home](#) : [Products](#) : [Switches](#) : [MICRO SWITCH™ Limit Switches](#) : [MICRO SWITCH™ Global Limit Switches](#) : [OP](#))

Enclosed Switch Series OP: Side Rotary, Fixed lever length with steel roller, 1NO 1NC Snap Action SPDT, CW or CCW actuation, No return lever, No mounting bracket furnished

Actual product appearance may vary.

Product Specifications

Availability	Global
Operating Force (OF)	0,56 N [2 oz]
Product Type	Enclosed Switches
Actuator	Side Rotary
Lever Type	1.5 in Fixed Length Lever with back mounted Steel Roller (.75 in dia. x .25 in wide)
Circuitry	1NC 1NO Snap Action, SPDT
Ampere Rating	15 A
Supply Voltage	125 Vac, 250 Vac, 480 Vac
Housing Material	Aluminum Die-Cast
Termination Type	0.5 in - 14NPT Conduit
Series Name	OP
Sealing	NEMA 1, 3, 4, 13
UL File #	E12252
Comment	CW or CCW actuation. No lever return spring. No mounting bracket furnished. Field adjustable through 360 degrees. Roller lever may be positively locked at intervals of approx. 0.2 degrees
Agency Approvals and Standards	UL, CSA
UNSPSC Code	39122213
UNSPSC Commodity	39122213 Limit Switches