


NOTES:

1. FOR USE WITH COMMSCOPE 77538 & BELDEN 1855A & 1865A CABLES.
2. FOR CABLING INSTRUCTIONS SEE 3-661-1.
3. FOR CRIMPING USE DIE KTH-2025.
4. CENTER CONTACT, 1-6690-7MA9, AND K-GRIP SLEEVE 1-33983-1M06 SUPPLIED UNASSEMBLED.
5. INTERFACE PER MIL-STD-348, FIG. 301-1 (AS APPLICABLE).
6. MATERIAL SPECIFICATIONS:
 INSULATOR: TEFLON PER ASTM D4894.
 GASKET: SILICONE RUBBER PER ZZ-R765.
 SPRING WASHER AND OUTER CONTACT: BERYLLIUM COPPER PER ASTM B196.
 ALL OTHER METAL PARTS: BRASS PER ASTM B16.
7. FINISH SPECIFICATIONS:
 CENTER CONTACT: GOLD PER MIL-G-45204
 SPRING WASHER: SILVER PER QQ-S-365
 ALL OTHER METAL PARTS: NICKEL PER QQ-N-290

8. ELECTRICAL SPECIFICATIONS:
 IMPEDANCE: 75 OHMS
 WORKING VOLTAGE: 500 VOLTS RMS
 FREQUENCY RANGE: DC - 12 GHz
 RETURN LOSS: -30dB MAX TO 3.0 GHz
 -20dB MAX TO 6.0 GHz
9. COMPLIANT TO 3G/6G/12G SDI SMPTE REQUIREMENTS.
10. MARK PACKAGE: KINGS 2065-11-9.

REV	DESCRIPTION	BY DATE	APPD
J	ER057798	04/10/15	YA



CATALOG P/N: 2065-11-9

PER ASME Y14.5M-1994 UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES [MM] TOLERANCES: DECIMAL: .XX [X.X] ± .01 [0.3] .XXX [X.XX] ± .005 [0.13] .XXXX [X.XXX] ± .XXXX ANGLES: ± 2° SCALE: 4:1				KINGS® by WINCHESTER Winchester Electronics Corporation ELECTRONICS 199 Park Road Ext Suite 104 Middlebury, Connecticut 06762			
CUSTOMER SALES DRAWING				75 OHM BNC PLUG FOR BELDEN 1855A OR EQUIVALENT CABLE (RoHS)			
DRAWN	DATE	APPROVED	DATE	A			
J	04/09/2015	MAR	07/28/2015				
APPROVED	DATE	APPROVED	DATE	SD2065-11-9			
YA	04/09/2015	XXX	XX/XX/XX				
				SHT	OF	REV	
				1	1	J	