






PCB板

技术要求:

- 特性阻抗 50Ω
- 频率范围 $0-6\text{GHz}$
- 接触电阻 内导体 $\leq 3\text{m}\Omega$
外导体 $\leq 2\text{m}\Omega$
- 绝缘电阻 $\geq 5000\text{M}\Omega$
- 盐雾时间 24H
- 分离力 $\geq 0.28\text{N}$
- 温度范围 -55°C T0 $+155^\circ\text{C}$

1	全螺铜座	1	黄铜	镀金
2	母针-尖头	1	黄铜	镀金
3	绝缘体	1	PTFE	
序号	名称	数量	材料	备注



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ± 0.30 X.XX ± 0.25 X.XXX ± 0.15 X' $\pm 2'$ X.X' $\pm 0.5'$ UNIT: mm [inch] SCALE: 1:1 SIZE: A4	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: SMA 180° DIP 正脚带孔 L17.5	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	HYCW22-SMAW1253-1750B
	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO:	HYC-2211241342
			SHEET NO.	1 OF 1