






注記

1. 材質：PBT

④ 2. かん合相手品番 : 7122-6329. 7122-6329-40

4. 適用端子番 : 7116-2990-02, 7116-2991-02, 7116-2992-02

: 7116-2927-02, 7116-2928-02, 7116-2929-02

## NOTES

## 1. MATERIAL : PBT

2. MATING PART NO. : 7122-6329. 7112-6329-40

3. APPLICABLE TERMINAL NO. : 7116-2990-02, 7116-2991-02, 7116-2992-02

: 7116-2927-02. 7116-2928-02. 7116-2929-02.



A

|                   |            |                       |          |        |        |       |       |
|-------------------|------------|-----------------------|----------|--------|--------|-------|-------|
| 4                 | 2013/09/17 | CHANGED FORM, ETC., B | C13-Z421 | M.M    |        |       |       |
| 3                 | 2010/11/15 | CHANGED PART NAME     | C10-ZB06 | G.M    |        |       |       |
| 2                 | 2000/12/13 | CHANGED FORM, A       | C00-M535 | H.Y    |        |       |       |
| 1                 | 1999/11/23 | CHANGED FORM ETC.     | C99-M745 | H.Y    |        |       |       |
|                   | 1999/07/13 | NEW                   | C39-M181 | H.Y    |        |       |       |
| LET               | DATE       | REVISION RECORD       | NO.      | CHKD   |        |       |       |
| GENERAL TOLERANCE |            |                       |          |        |        |       |       |
|                   | 10MAX      | 50MAX                 | 100MAX   | 250MAX | 250OVR | ANGLE | ECENT |
| A                 | ±0.15      | ±0.2                  | ±0.3     | ±0.5   | ±0.75  | ±30'  | 0.1   |
| B                 | ±0.2       | ±0.3                  | ±0.55    | ±0.95  | ±1.4   | ±30'  | 0.1   |
| C                 | ±0.3       | ±0.5                  | ±0.8     | ±1.4   | ±2     | ±30'  | 0.15  |
| SPECIFIED         |            |                       |          |        |        | MASS  |       |

|                                         |            |                  |        |            |       |                   |                |            |
|-----------------------------------------|------------|------------------|--------|------------|-------|-------------------|----------------|------------|
| CUSTOMER                                |            | MATERIAL SPEC.   |        | SEE NOTES  |       | TREAT. & FIN.     |                | ISSUE MARK |
| CUSTOMER PART NO.                       |            | CUSTOMER DWG NO. |        |            |       |                   |                |            |
| OFFICE                                  |            | TRIAL PART NO.   |        |            |       |                   |                |            |
| VENDOR                                  |            |                  |        |            |       |                   |                |            |
| VENDOR NO.                              |            |                  |        |            |       |                   |                |            |
| DWG TYPE                                | DWG SOURCE | DWG DATE         | UNIT   | SCL        | ANGLE |                   |                |            |
| R                                       | NEW        | 1999/07/13       | mm     | 2 : 1      | 3     |                   |                |            |
| APPROVED                                | CHECKED    | CHECKED          | DESIGN | DRAWN      |       | PART NO. CHL CODE | 7123-6329 ETC. |            |
|                                         |            |                  |        |            |       | DWG NO.           | 7123-6329:R    |            |
|                                         |            |                  |        |            |       | SET DWG NO.       |                |            |
| T. YAMAWAKI S. NEMOTO YOSHIDA M. MIGUEL |            |                  |        |            |       |                   |                |            |
| 2013/09/17                              |            | 2013/09/17       |        | 1999/06/07 |       | 2013/09/17        |                |            |
| YAZAKI CORPORATION                      |            |                  |        |            |       |                   |                |            |