




REV.	MODIFICATION.	DATE	DRN
01	NEW DRAWING	17/11/04	NJB
02	ECN 04-227	10/12/04	NJB
03	ECN 07-220	06/12/07	NJB





FC-320-NV
FUSE COVER



FH-320-NV
FUSE HOLDER



TYPICAL APPLICATION VIEW




NOTES:
1) ALL PRIMARYDIMENSIONS IN mm,
SECONDARY DIMENSIONS IN [INCHES].

INFORMATION CONTAINED IN THIS DOCUMENT IS CONFIDENTIAL TO RICHCO INTERNATIONAL Co. Ltd. AND MAY NOT BE DISCLOSED OR REPRODUCED IN WHOLE OR PART WITHOUT THEIR WRITTEN CONSENT



METRIC GENERAL TOLERANCES ±0.25
ARE PRIMARY UNLESS OTHERWISE STATED
1 DECIMAL PLACE ±
2 DECIMAL PLACES ±
ANGULAR ±1°
IMPERIAL GENERAL TOLERANCES ±0.010
ARE FOR REFERENCE UNLESS OTHERWISE STATED
1 DECIMAL PLACE ±
2 DECIMAL PLACES ±
ANGULAR ±1°

MATERIAL: NYLON 6/6 25% GF (RMS-49)				COLOUR: BLACK	
TITLE: FUSE COVER				PART No: FC-320-NV	
DRG No: 04-164		NPR REF:			SIZE A4
DRN NJB	DATE 17/11/04	CHKD OW	DATE 17/11/04		
SCALE NTS		SHEET No 1 OF 1			
E				F	
FORM No 0145/02					