

未注标准按:GB/T6892-2015执行!																																																																														
模具类型	分流模 ☐ 平面模 ☒																																																																													
未注型材形位公差按GB/T14846-2014执行!																																																																														
※除非特殊标明, 否则按上述要求管控!																																																																														
<table><tr><td colspan="2">修改记录</td><td rowspan="2">客户确认:</td><td>范 围</td><td>公 差 值</td><td colspan="2">技 术 参 数</td><td colspan="2" rowspan="2">深圳市文豪五金制品有限公司</td></tr><tr><td>次数</td><td>修改时间</td><td>20.0MM-LESS</td><td>±0.10</td><td>载面积</td><td>MM²</td></tr><tr><td>原版-A</td><td></td><td rowspan="10">客户图号:</td><td>21.0-49.0MM</td><td>±0.15</td><td>理论重量</td><td>KG/M</td><td>本厂编号</td><td rowspan="5">6063-T5</td></tr><tr><td>原版-A (1)</td><td></td><td>50.0-69.0MM</td><td>±0.20</td><td>硬 度</td><td></td><td>材 质</td></tr><tr><td>原版-A (2)</td><td></td><td>70.0-99.0MM</td><td>±0.25</td><td>使用机型</td><td>T</td><td>制 图</td><td>陈 廷 舜</td><td>日 期</td><td>2025-06-30</td></tr><tr><td>原版-A (3)</td><td></td><td>100.0-149.0MM</td><td>±0.30</td><td>定尺长度</td><td>M</td><td>比 例</td><td>4:1</td><td></td></tr><tr><td>原版-A (4)</td><td></td><td>150.0-199.0MM</td><td>±0.40</td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>原版-A (5)</td><td></td><td>200.0-249.0MM</td><td>±0.50</td><td></td><td></td><td></td><td></td><td></td></tr><tr><td></td><td></td><td>250.0MM以上</td><td>±0.60</td><td></td><td></td><td></td><td></td><td></td></tr></table>		修改记录		客户确认:	范 围	公 差 值	技 术 参 数		深圳市文豪五金制品有限公司		次数	修改时间	20.0MM-LESS	±0.10	载面积	MM ²	原版-A		客户图号:	21.0-49.0MM	±0.15	理论重量	KG/M	本厂编号	6063-T5	原版-A (1)		50.0-69.0MM	±0.20	硬 度		材 质	原版-A (2)		70.0-99.0MM	±0.25	使用机型	T	制 图	陈 廷 舜	日 期	2025-06-30	原版-A (3)		100.0-149.0MM	±0.30	定尺长度	M	比 例	4:1		原版-A (4)		150.0-199.0MM	±0.40						原版-A (5)		200.0-249.0MM	±0.50								250.0MM以上	±0.60					
修改记录		客户确认:	范 围		公 差 值	技 术 参 数		深圳市文豪五金制品有限公司																																																																						
次数	修改时间		20.0MM-LESS	±0.10	载面积	MM ²																																																																								
原版-A		客户图号:	21.0-49.0MM	±0.15	理论重量	KG/M	本厂编号	6063-T5																																																																						
原版-A (1)			50.0-69.0MM	±0.20	硬 度		材 质																																																																							
原版-A (2)			70.0-99.0MM	±0.25	使用机型	T	制 图		陈 廷 舜	日 期	2025-06-30																																																																			
原版-A (3)			100.0-149.0MM	±0.30	定尺长度	M	比 例		4:1																																																																					
原版-A (4)			150.0-199.0MM	±0.40																																																																										
原版-A (5)			200.0-249.0MM	±0.50																																																																										
			250.0MM以上	±0.60																																																																										