



Suggested Panel Opening:



UNIT: mm / inch
Tolerances: ± 0.10 / 0.004

Keep-Out Area (Component Side View):





UNIT: mm / inch
Tolerances: ± 0.10 / 0.004

TOLERANCE TABLE	
.0	± 0.30
.00	± 0.20
.000	± 0.05

APPROVED:	DATE:	CkmtwCHANKEMENG INDUSTRYCO., LTD			
CHECKED:	DATE:	TITLE:			
DRAWN:	DATE:	RJ45-8P/8C 直插 带灯 带屏蔽带变压器			
SXA	2019-06-21	PART. NO. R-RJ45S08P-D001			
UNIT	mm	SCALE	free	REV.	A
FILE NO.	Ckmtw-RJ45-0194	REV.	A	KYD0	

客户确认	
日期	



Electrical:

- Turn ratio:1~2:J1~J2=1CT:1CT(±2%).
6~7:J3~J6=1CT:1CT(±2%).
- OCL:350uH Min.at 100KHz 100mV 8mA DC.
- Insertion Loss: -1.0 dB Max 1~100MHz.
- Return loss: -20dB Min 1~10MHz;
-16dB Min 10~30MHz.
-12dB Min 30~60MHz.
-10dB Min 60~80MHz.
- Cross talk: -40dB Min 1~30MHz;
-35dB Min 30~60MHz;
-30dB Min 60~100MHz;
- CMR: -30dB Min 1~100MHz;
- Hi-Pot:1500V AC & 2250V DC
6S 1 mA PRI TO SEC

LED Specification


Standard LED Color	LED Wavelength	Forward(A)	Forward(V)
Green	568nm	20mA	1.85-2.45V
Yellow	585nm	20mA	1.7-2.2V

APPROVED:	DATE:	C km tw CHANKEMENG INDUSTRYCO., LTD			
CHECKED:	DATE:	TITLE: RJ45-8P/8C 直插 带灯带屏蔽带变压器			
DRAWN:	DATE:	PART P/N	R-RJ45S08P-D001		
SXA	2019-06-21	UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-RJ45-0194	REV.	A
		KYD0			

TOLERANCE TABLE	
.0	±0.30
.00	±0.20
.000	±0.05

客户确认	
日期	

PROFILE OF WAVE SOLDER



A.Preheating B.Soldering C.Gradual Cooling
 Tip temperature:260±5°C.
 Tip temperature time:5Sec Max.
 Tip melting point of Sn96.5/Ag3/Cu0.5:217°C.

Remarks: after wave soldering, the plastic positioning columns of the product which under the PCB will be slightly melted, but it won't affect its function.

APPROVED:		DATE:		C kmtw CHANKEMENG INDUSTRYCO., LTD 深圳市灿科盟实业有限公司							
CHECKED:		DATE:		TITLE: RJ45-8P/8C 直插 带灯带屏蔽带变压器							
TOLERANCE TABLE				PART P/N		R-RJ45S08P-D001					
.0	±0.30	DRAWN:		DATE:		UNIT	mm	SCALE	free		
.00	±0.20	SXA		2019-06-21		FILE NO.	Ckmtw-RJ45-0194	REV.	A	KYD0	
.000	±0.05										