





REV.	REVISION DESCRIPTION	DATE	APPD

技术要求 (Technical requirements) :

- 1. 材质 (material): 黄铜 (brass)
- 2. 材料规格 (Material specifications) : 0.35mm
- 3. 压线范围 (Wire) : AWG24#--14#
- 4. 表面处理 (Surface treatment) : 锡 (Tin plated)
- 5. 额定电压 Rated voltage : 300V AC.DC.
- 6. 额定电流 Rated current : 15A AC.DC.
- 7. 接触电阻 Contact resistance: 20mΩ MAX
- 8. 绝缘电阻 Insulation resistance: 1000 MΩ MIN
- 9. 耐压 Withstand voltage: 2000V AC/minute
- 10. 配 0.5/0.8mm 插片

Product name	Dimension mm			
	A1	B1	A2	B2
DL187ZCDJ	4.0	4.4	2.3	2.8
DL187ZCZJ	4.75	4.9	3.0	3.0
DL187ZCGJ	5.5	5.7	3.8	3.8

GENERAL TOLERANCES (UNLESS SPECIFIED)		浙江德利接插件有限公司			
		ZHEJIANG DELI CONNECTORS CO.,LTD			
. X: ±0.25	. X° : ±3.0°	PRODUCT NAME:		TITLE:	
. XX: ±0.15	. XX° : ±2.0°	DL187ZCxx		187	
. XXX: ±0.01	. XXX° : ±1.0°	DR. :Chen Quan Long	DATE. :21.04.11	PART. NO. :	
FINISH:		CHKD. :Wu Hui	DATE. :21.04.11	SCALE: N/A	PAGE: 1/1
DRAWING NO. :		APPD. :Ren An De	DATE. :21.04.11	UNITS: mm	REV. : A




7		8	
REV.	REVISION DESCRIPTION	DATE	APPD

技术要求 (Technical requirements) :

1. 材质 (material): 黄铜 (brass)
2. 材料规格 (Material specifications) : 0.3mm
3. 压线范围 (Wire) : AWG22#--14#
4. 表面处理 (Surface treatment) : 锡 (Tin plated)
5. 额定电压 Rated voltage : 300V AC.DC.
6. 额定电流 Rated current : 15A AC.DC (MAX).
7. 接触电阻 Contact resistance: 20mΩ (MAX)
8. 绝缘电阻 Insulation resistance: 1000 MΩ (MIN)
9. 耐压 Withstand voltage: 2000V AC/minute
10. 配 0.5/0.8mm 插片

Product name	Dimension mm				Applicable wires
	A1	B1	A2	B2	AWG#
DL187ZCDS DJ	4.5	4.5	2.7	2.3	22-18
DL187ZCDS ZJ	5.0	5.2	3.2	3.4	18-16
DL187ZCDS GJ	5.4	5.4	3.6	4.0	16-14

GENERAL TOLERANCES (UNLESS SPECIFIED)		浙江德利接插件有限公司 ZHEJIANG DELI CONNECTORS CO.,LTD			
. X: ±0.25	. X° : ±3.0°	PRODUCT NAME: DL187ZCDSxx		TITLE: 187	
. XX: ±0.15	. X° : ±2.0°	DR. :Chen Quan Long	DATE. :21.04.11	PART. NO. :	
. XXX: ±0.01	. XX° : ±1.0°	CHKD. :Wu Hui	DATE. :21.04.11	SCALE: N/A	PAGE: 1/1
FINISH: _____		APPD. :Ren An De	DATE. :21.04.11	UNITS: mm	REV. : A
DRAWING NO. :					




7		8	
REV.	REVISION DESCRIPTION	DATE	APPD

技术要求 (Technical requirements) :

- 1. 材质 (material): 黄铜 (brass)
- 2. 材料规格 (Material specifications) : 0.4mm
- 3. 压线范围 (Wire) : AWG18#--14#
- 4. 表面处理 (Surface treatment) : 亚光 (yaguan)
- 5. 额定电压Rated voltage :250V AC.DC.
- 6. 额定电流Rated current : 10A AC.DC.
- 7. 接触电阻Contact resistance: 20mΩ MAX
- 8. 绝缘电阻Insulation resistance: 1000 MΩ MIN
- 9. 耐压Withstand voltage: 1500V AC/minute
- 10. 配0.5/0.8mm插片





GENERAL TOLERANCES (UNLESS SPECIFIED)		浙江德利接插件有限公司			
		ZHEJIANG DELI CONNECTORS CO.,LTD			
. X: ±0.25	X° : ±3.0°	PRODUCT NAME:		TITLE:	
. XX: ±0.15	. X° : ±2.0°	DL187ZCJB		187	
. XXX: ±0.01	. XX° : ±1.0°	DR. :Chen Quan Long	DATE. :21.04.11	PART. NO. :	
FINISH:		CHKD. :Wu Hui	DATE. :21.04.11	SCALE: N/A	PAGE: 1/1
DRAWING NO. :		APPD. :Ren An De	DATE. :21.04.11	UNITS: mm	REV. : A



技术要求 (Technical requirements) :


1. 材质 (material): 黄铜 (brass)
2. 材料规格 (Material specifications) : 0.35mm
3. 压线范围 (Wire) : AWG20#--14#
4. 表面处理 (Surface treatment) : 锡 (Tin plated)
5. 额定电压 Rated voltage : 300V AC.DC.
6. 额定电流 Rated current : 15A AC.DC.
7. 接触电阻 Contact resistance: 20mΩ MAX
8. 绝缘电阻 Insulation resistance: 1000 MΩ MIN
9. 耐压 Withstand voltage: 2000V AC/minute
10. 配0.5/0.8mm插片

GENERAL TOLERANCES (UNLESS SPECIFIED)		浙江德利接插件有限公司 ZHEJIANG DELI CONNECTORS CO.,LTD			
. X: ±0.5 X° : ±3.0°		PRODUCT NAME: DL187QX		TITLE: 187	
. XX: ±0.35 . X° : ±2.0°		DR.:Zhang Wen Jing DATE.:10.04.1		PART. NO.:	
. XXX: ±0.10 . XX° : ±1.0°		CHKD.:Liu Bing DATE.:10.04.1		SCALE: N/A PAGE: 1/1	
FINISH: _____		APPD.:Ren An De DATE.:10.04.1		UNITS: mm REV. : A	
					
DRAWING NO.:					




技术要求 (Technical requirements) :

1. 材质 (material): 黄铜 (brass)
2. 材料规格 (Material specifications) : 0.3mm
3. 压线范围 (Wire) : AWG18#--14#
4. 表面处理 (Surface treatment) : 锡 (Tin plated)
5. 额定电压 Rated voltage : 300V AC.DC.
6. 额定电流 Rated current : 15A AC.DC.
7. 接触电阻 Contact resistance: 10mΩ MAX
8. 绝缘电阻 Insulation resistance: 1000 MΩ MIN
9. 耐压 Withstand voltage: 2000V AC/minute
10. 配 0.5/0.8mm 插片

GENERAL TOLERANCES (UNLESS SPECIFIED)			浙江德利接插件有限公司 ZHEJIANG DELI CONNECTORS CO.,LTD			
.X: ±0.25	X° : ±3.0°	PRODUCT NAME: DL187QXDS		TITLE: 187		
.XX: ±0.15	.X° : ±2.0°	DR. :Chen Quan Long		DATE. :20.04.1		
.XXX: ±0.01	.XX° : ±1.0°	CHKD. :Wu Hui		DATE. :20.04.1		
FINISH: 		APPD. :Ren An De		DATE. :20.04.1		
DRAWING NO. :				UNITS: mm		
				SCALE: N/A		
				PAGE: 1/1		
				REV. : A		


REV.	ECN. NO.	REVISION DESCRIPTION	DATE	APPD



技术参数 (SPECIFICATIONS)

额定电压 (Voltage rating): 300V, AC, DC
额定电流 (Current rating): 15A
接触电阻 (Contact resistance): $\leq 0.02 \Omega$
绝缘电阻 Insulation resistance: 1000 M Ω MIN
耐压 Withstand voltage: 1500V AC/minute
材质 (material): 黄铜 (brass)
材料规格 (Material specifications): 0.5mm
表面处理 (Surface treatment): 镍底镀锡 (Nickel bottom tin)



GENERAL TOLERANCES (UNLESS SPECIFIED)		浙江德利接插件有限公司 ZHEJIANG DELI CONNECTORS CO.,LTD			
.X: ± 0.25	.X°: $\pm 3.0^\circ$	PRODUCT NAME: DL1870122ST0.5		TITLE: 187	
.XX: ± 0.15	.XX°: $\pm 2.0^\circ$	DR.: Chen Quan Long	DATE.: 21.11.08	PART. NO.:	
.XXX: ± 0.01	.XXX°: $\pm 1.0^\circ$	CHKD.: Wu Hui	DATE.: 21.11.08	SCALE: N/A	PAGE: 1/1
FINISH:		APPD.: Ren An De	DATE.: 21.11.08	UNITS: mm	REV.: A
DRAWING NO.:					



技术参数 (SPECIFICATIONS)

- 额定电压 (Voltage rating): 300V, AC, DC
额定电流 (Current rating): 15A
接触电阻 (Contact resistance): ≤0.02Ω
绝缘电阻 Insulation resistance: 1000 MΩ MIN
耐压 Withstand voltage: 1500V AC/minute
材质 (material): 黄铜 (brass)
材料规格 (Material specifications): 0.8mm
表面处理 (Surface treatment): 镍底镀锡 (Nickel bottom tin)

GENERAL TOLERANCES (UNLESS SPECIFIED)		浙江德利接插件有限公司 ZHEJIANG DELI CONNECTORS CO.,LTD			
.X: ±0.25	.X°: ±3.0°	PRODUCT NAME: DL1870122ST0.8		TITLE: 187	
.XX: ±0.15	.XX°: ±2.0°	DR.: Chen Quan Long	DATE.: 21.11.08	PART. NO.:	
.XXX: ±0.01	.XXX°: ±1.0°	CHKD.: Wu Hui	DATE.: 21.11.08	SCALE: N/A	PAGE: 1/1
FINISH:		APPD.: Ren An De	DATE.: 21.11.08	UNITS: mm	REV.: A
DRAWING NO.:					



技术参数 (SPECIFICATIONS)

额定电压 (Voltage rating): 300V, AC, DC

额定电流 (Current rating): 15A

接触电阻 (Contact resistance): $\leq 0.02 \Omega$

绝缘电阻 Insulation resistance: 1000 M Ω MIN


耐压 Withstand voltage: 2000V AC/minute


材质 (material): 黄铜 (brass)

材料规格 (Material specifications): 0.5mm

表面处理 (Surface treatment): 镍底镀锡 (Nickel bottom tin)


GENERAL TOLERANCES (UNLESS SPECIFIED)		浙江德利接插件有限公司 ZHEJIANG DELI CONNECTORS CO.,LTD			
. X: ± 0.25	. X°: $\pm 3.0^\circ$	PRODUCT NAME: DL1870222ST0.5		TITLE: 187	
. XX: ± 0.15	. XX°: $\pm 2.0^\circ$	DR.: Chen Quan Long	DATE.: 21.11.08	PART. NO.:	
. XXX: ± 0.01	. XXX°: $\pm 1.0^\circ$	CHKD.: Wu Hui	DATE.: 21.11.08	SCALE: N/A	PAGE: 1/1
FINISH:		APPD.: Ren An De	DATE.: 21.11.08	UNITS: mm	REV.: A
DRAWING NO.:					





技术参数 (SPECIFICATIONS)
温度范围 (Temperature range): $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$
额定电压 (Voltage rating): 300V, AC, DC
额定电流 (Current rating): 15A
接触电阻 (Contact resistance): $\leq 0.02 \Omega$
绝缘电阻 (Insulation resistance): 常温 $\geq 1000\text{M}\Omega$
材料 (Material): 壳体 (Housing): 尼龙 (Nylon)

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO., LTD			
.X: ± 0.25	X°: $\pm 3.0^{\circ}$	PRODUCT NAME: DL187ZCYHT		TITLE: Sheath Series	
.XX: ± 0.15	.X°: $\pm 2.0^{\circ}$	DR: Yuan Jun Rong	DATE: 22/08/01	PART NO:	
.XXX: ± 0.01	.XX°: $\pm 1.0^{\circ}$	CHKD: Wu Hui	DATE: 22/08/01	SCALE: N/A	PAGE: 1/1
FINISH:		APPD: Ren An De	DATE: 22/08/01	UNITS: mm	REV.: A
DRAWING NO:					



REV.	REVISION DESCRIPTION	DATE	APPD

技术参数 (SPECIFICATIONS)

温度范围 (Temperature range): -25℃~85℃
额定电压 (Voltage rating): 300V, AC, DC
额定电流 (Current rating): 8~15A
接触电阻 (Contact resistance): ≤0.02Ω
绝缘电阻 (Insulation resistance): 常温≥1000MΩ
阻燃性 (combustion resistance): ULVW-1(FV-0)
材料 (Material): 壳体 (Housing): PVC

Product name	Dimension (mm)
	D
DL187ZCRHT2.5	2.5
DL187ZCRHT3.0	3.0
DL187ZCRHT3.2	3.2
DL187ZCRHT	3.5
DL187ZCRHT4.0	4.0

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO ., LTD			
. X: ± 0.25	X° : ± 3.0°	PRODUCT NAME: DL187ZCRHTxx		TITLE: Sheath Serie	
. XX: ± 0.15	. X° : ± 2.0°	DR: Chen Quan Long	DATE: 21/11/23	PART NO:	
. XXX: ± 0.01	. XX° : ± 1.0°	DR: Wu Hui	DATE: 21/11/23	SCALE: N/A	PAGE: 1/1
FINISH:		APPD: Ren An De	DATE: 21/11/23	UNITS: mm	REV.: A
DRAWING NO:					