











PCB LAYOUT



SPECIFICATIONS

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25℃~+85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 1000V AC/minute
- 7、Material:Wafer PA46, UL94V-0
PIN Brass Tin-plated

GENERL TOLERANCE		制 图	张迎春	料 号	KH-A2508-2X06A	版 本	A
X.±0.25	X.°±2°	Mapping	2022、09、16	PART NO.	XA双排直针 WAFER DIP TYPE	REV.	
.X±0.25	.X°±1°	审 核	钱岳生	品 名		页 次	1/1
.XX±0.15	.XX°±0.5°	Audit	2022、09、16	TITLE		SHEET	
.XXX±0.10	.XXX°±0.5°	核 准	张 名	客户料号	深圳市金航标电子有限公司		
		Approved	2022、09、17	CUTM. NO.			
		单 位	mm	比 例	www.kinghelm.com		
		Units		SCALE			