









版本 REV.	日期 DATE	ECN NO.	变更内容 DESCRIPTION	制图 DRAWN



SPECIFICATIONS

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperaturer Range: -25°C ~ +85°C
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 1000V AC/minute
- 7、Material:Wafer PA46, UL94V-0
PIN Brass Tin-plated

GENERAL TOLERANCE		制图 Mapping	张迎春		料号 PART NO.	KH-A2508-2X11A	版本 REV.	A
X.±0.25	X.°±2°		2022、09、16	钱岳生				
.X.±0.25		审核 Audit	2022、09、16		客户料号 CUTM. NO.	XA双排直针 WAFER DIP TYPE	页次 SHEET	1/1
.XX±0.15			张名					
.XXX±0.10		核准 Approved	2022、09、17		.XX°±0.5°	Units	mm	比例 SCALE

深圳市金航标电子有限公司
www.kinghelm.com