








技术特性:

使用条件: $-30\sim 70^{\circ}$
额定负荷: DC30V 1.5A
接触电阻: $\leq 0.03\Omega$
绝缘电阻: $\geq 100M\Omega$ DC250V
耐压: AC500V(50Hz) 1min
插拔力: 3~20N
寿命: 5000次

线路板开孔尺寸



电路原理图



7	屏蔽盖	1	H62黄铜带(Y) $\delta=0.25mm$	铜锡
6	弯片	1	H62黄铜带(Y) $\delta=0.30mm$	铜锡
5	插针	1	H62黄铜棒	铜锡
4	后盖	1	PBT	黑
3	平片	1	H62黄铜带(Y) $\delta=0.30mm$	铜锡
2	簧片	1	65Mn 锰钢带 $\delta=0.20mm$	锡锡
1	底座	1	PBT	黑
序号	名称	数量	材料	备注

GENERAL TOLERANCES				
0.X	± 0.30	X°	$\pm 3^{\circ}$	
0.XX	± 0.20			
0.XXX	± 0.10	X.X°	$\pm 1^{\circ}$	
UNIT	SIZE	SCALE		
MM	A4	1:1		

DRAWN		C	TITLE: 电源插座	
DESIGN			PART NO.	DC-005G-**
CHECKED			PRODUCT NO.	
APPROVED			DRAWING NO.	
UNIT: mm SCALE: 1:1 REV: 01-1 SHT: 1 OF 1				

浙江创都电子科技有限公司

ECN NO.	REV	DATE	DESCRIPTION	MDF'D	APP'D
	01	2025.03.07	NEW DRAWING RELEASE		