

1

2

3



4

RoHS

Specifications(规格):

- 1.Impedance(特性阻抗): 50Ω;
- 2.Frequency(工作频率): DC~20GHz;
- 3.VSWR(电压驻波比): 1.20 Max.@18GHz;
- 4.Insulation resistance(绝缘阻抗): $\geq 1000M\Omega$;
- 5.Dielectric withstand voltage(介质耐电压): $\geq 500V$ AC;
- 6.Mating cycles(耐久性): ≥ 500 cycles;
- 7.Temperature range(使用温度): $-40^{\circ}C \sim +125^{\circ}C$;

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE		

3D View

ANGULAR	$\pm 5^{\circ}$
X.	± 0.50
X.x	± 0.20
X.xx	± 0.10
X.xxx	± 0.05
UNSPECIFIED TOLERANCES	

3	Center Conductor	Beryllium Bronze	Gold PLATED	1 PC	
2	Dielectric	PTFE		1 PC	
1	Outer Conductor	Brass/SUS	Ni PLATED/Passivation	1 PC	
NO.	NAME	MATERIAL	FINISH (Contact)	Q'TY	Note

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn



DESIGN	希文	VIEW:
CHECKED		UNIT: mm/in
APPROVED		SIZE: A4

XKB INDUSTRIAL PRECISION CO.,LIMITED

MODEL TYPE: SMA/FAKRA Adapter		
PART NO.: XMADFK-5FMS20-CG02		
DWG NO.: X-XMADFK-5FMS20-CG02		
SCALE N/A	PAGE 1/1	REVISION A0