







RoHS





3D VIEW

Connector PIN assignment

| PIN NO. | Signal Name |
|---------|-------------|
| PIN-1   | VBUS        |
| PIN-2   | D-          |
| PIN-3   | D+          |
| PIN-4   | GND         |



Recommended connector arrangement

Panel opening size  
(Recommended panel thickness:1.0mm)Recommend P.C.B LAYOUT  
(Recommended P.C.B thickness:1.20~1.60mm)

| PART NO.       | Coding/Colour      |
|----------------|--------------------|
| XLBWM39T-024-A | <br>A Coding/Black |
| XLBWM39T-024-C | <br>C Coding/Blue  |
| XLBWM39T-024-F | <br>F Coding/Brown |
| XLBWM39T-024-E | <br>E Coding/Green |

|                        |       |
|------------------------|-------|
| ANGULAR                | ±5°   |
| X.                     | ±0.50 |
| X.x                    | ±0.20 |
| X.xx                   | ±0.10 |
| X.xxx                  | ±0.10 |
| UNSPECIFIED TOLERANCES |       |

|     |            |                 |                  |       |      |
|-----|------------|-----------------|------------------|-------|------|
| 4   | Long PIN   | Copper Alloy    | Gold PLATED      | 2 PCS |      |
| 3   | Short PIN  | Copper Alloy    | Gold PLATED      | 2 PCS |      |
| 2   | Dielectric | PA9T            |                  | 1 PC  |      |
| 1   | SHELL      | Stainless steel | Ni PLATED        | 1 PC  |      |
| NO. | NAME       | MATERIAL        | FINISH (Contact) | Q'TY  | Note |

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn

XKLB 星城  
Connection

|          |    |             |                                                |
|----------|----|-------------|------------------------------------------------|
| DESIGN   | 希文 | VIEW:       | MODEL TYPE:<br>TAK 4PIN Connector, Right Angle |
| CHECKED  |    | UNIT: mm/in | PART NO.:<br>XLBWM39T-024-X                    |
| APPROVED |    | SIZE: A4    | DWG NO.:<br>X-XLBWM39T-024-X                   |

XKB INDUSTRIAL PRECISION CO.,LIMITED

|       |      |          |
|-------|------|----------|
| SCALE | PAGE | REVISION |
| N/A   | 1/1  | A0       |