









版本 REV.	日期 DATE	ECN NO.	变更内容 DESCRIPTION	制图 DRAWN



SPECIFICATIONS

- Current Rating: 3A AC, DC
- Voltage Rating: 250V AC, DC
- Temperaturer Range: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$
- Contact Resistance: $20\text{m}\Omega$ Max
- Insulation Resistance: $1000\text{M}\Omega$ Min
- Withstanding Voltang: 1000V AC/minute
- Material:Wafer PA46, UL94V-0
PIN Brass Tin-plated



GENERAL TOLERANCE		制图 Mapping	张迎春		料号 PART NO.	KH-A2508-2X08A	版本 REV.	A
X.±0.25	X.°±2°		2022、09、16	钱岳生				
$.X\pm0.25$		审核 Audit	2022、09、16		客户料号 CUTM. NO.	XA双排直针 WAFER DIP TYPE	页次 SHEET	1/1
$.X\pm0.25$			张名					
$.XX\pm0.15$		核准 Approved	2022、09、17		单位 Units	mm	比例 SCALE	
$.XXX\pm0.10$			$XXX\pm0.5^{\circ}$					

深圳市金航标电子有限公司
www.kinghelm.com