


#### SCHEMATIC



PIN	Ø2.0	Ø2.5	
APPD.			

#### SPECIFICATION

- 1.Rating : DC 30V 0.5A;
- 2.Contact resistance:  $\leq 0.03\Omega$ ;
- 3.Insulation resistance:  $\geq 100M\Omega$  (DC250V);
- 4.Withstand voltage: 500VAC ;
- 5.Insertion and extraction force: 3~20N;
- 6.life test: 5,000 cycles .

NO.	DESCRIPTION	QTY	MATERIAL	PLATING
6	HOUSING	1	PA66	
5	AXIS SUPPORT	1	H59 BRASS	Ni-Plating
4	PIN	1	H59 BRASS	Ni-Plating
3	SPRING	1	PHOSPHOR BRONZE	Cu-Sn-Plating
2	CURVE PIECE	1	PHOSPHOR BRONZE	Cu-Sn-Plating
1	FLAT PIECE	1	H62 BRASS	Cu-Sn-Plating

UNIT: MM	TYPE:	MODEL NO:	PAPER NO:		PAGE 1 OF 1	
			A4	TOLERANCES	SCALE	VER
	DC JACK	DC-026M	±0.15	±1.5°	3:1	1
DESIGNER						
BY						
CHECK						
BY						
APPROVED						

浙江创都电子科技有限公司