








REV.	ECN NO.	DESCRIPTION	DRAW	APPD.	DATE
A	---	新版本发行			2022.10.10

- NOTES:
- SPECIFICATION:
- CURRENT RATING: 5.0A MAX
 - VOLTAGE: 100 VAC
 - TEMPERATURE RANGE: -30 °C ~ 85 °C
 - CONTACT RESISTANCE: 40 MILLIONHM MAX
 - INSULATION RESISTANCE: 100 MEGOHMS MIN.
 - INSERTION FORCE : 5N~20N
 - UNMATING FORCE: 8N~20N
 - DURABILITY: 10,000 CYCLES



SECTION:A-A



RECOMMENDED PCB LAYOUT(TOP VIEW)

THICKNESS 0.80MM;DEFAULT TOLERANCE:±0.05

7	COVER SHELL	STAINLESS STEEL	NI Plated	1PCS
5	SHIELDING PLATE	STAINLESS STEEL	---	1PCS
4	MD	HIGH TEMPERATURE PLASTIC	BLACK	1PCS
3	CONTACT	COPPER ALLOY	Au/Ni, TIN Plated	1SET
2	CONTACT	COPPER ALLOY	Au/Ni, TIN Plated	1SET
2	HOUSING	HIGH TEMPERATURE PLASTIC	BLACK	1PCS
NO.	DESCRIPTION	MATERIAL	REMARKS	QTY

TOLERANCE	NAME(INTENDED USE)
X.X ±0.30 X.* ± 2*	CUSTOMER DRAWING
XX ±0.20 .X* ± 1*	PART NO.
.XXX ±0.10 .XX* ±0.5*	AAOB011-026N
UNITS	mm
MATERILA	APPD:
PIN	CHED:
SIGNAL NAME	DRAW:



TITLE:

USB C 母座16P 沉板1.6 带弹片和凸包

DRAWG NO.

A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SBUS2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBUS1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME
FINISH			
DRAW:			

SCALE	SHEET	REV.
1:1	1/2	A