



SCHEMATIC



P.C.B LAYOUT
TOP VIEW



PIN	Ø2.0	Ø2.5	
APPD.			

SPECIFICATION

1. Rating : DC 30V 5A;
2. Contact resistance: $\leq 0.03\Omega$;
3. Insulation resistance: $\geq 100M\Omega$ (DC250V);
4. Withstand voltage: 500VAC ;
5. Insertion and extraction force: 3-20N;
6. Life test: 5,000 cycles.

NO.	DESCRIPTION	QTY	MATERIAL	PLATING
6	HOUSING	1	PA66	
5	AXIS	1	BRASS	Ni-Plating
4	SUPPORT	1	H59 BRASS	Ni-Plating
3	SPRING	1	BRONZE	Cu-Sn-Plating
2	CURVE PIECE	1	H62 BRASS	Cu-Sn-Plating
1	FLAT PIECE	1	H62 BRASS	Cu-Sn-Plating
UNIT: MM	TYPE:	MODEL NO:	PAPER NO:	PAGE 1 OF 1
	DC JACK	DC-025BM	A4 TOLERANCE ANGLES SCALE VER	
DESIGNER BY			± 0.15	$\pm 1.5^\circ$
CHECK BY				3:1
APPROVED BY				1

浙江创都电子科技有限公司