





PIN	ø2.0	ø2.5	
APPD.			

- 1.Rating : DC 30V 5A;
- 2.Contact resistance: $\leq 0.03\Omega$;
- 3.Insulation resistance: $\geq 100M\Omega$ (DC250V);
- 4.Withstand voltage: 500VAC ;
- 5.Insertion and extraction force: 3–20N;
- 6.life test: 5,000 cycles.

6	HOUSING	1	PA66					
5	AXIS	1	BRASS	Ni-Plating				
4	SUPPORT	1	H59 BRASS	Ni-Plating				
3	SPRING	1	BRONZE	Cu-Sn-Plating				
2	CURVE PIECE	1	H62 BRASS	Cu-Sn-Plating				
1	FLAT PIECE	1	H62 BRASS	Cu-Sn-Plating				
NO.	DESCRIPTION	QTY	MATERIAL	PLATING				
UNIT: MM		TYPE: DC JACK	MODEL NO: DC-025BM	PAPER NO:		PAGE 1 OF 1		
				A4	TOLERANCES	ANGLES	SCALE	VER
				±0.15	±1.5°	3:1	1	
DESIGNER		浙江创都电子科技有限公司						
BY CHECK								
BY APPROVED								