


ROHS Compliant

MAPX	MODIFICATION	DATE	DRAW	APPROVE

General tolerances(mm)													0.1/10
0 ~ 3	>3 ~ 6	>6 ~ 10	>10 ~ 18	>18 ~ 30	>30 ~ 50	>50 ~ 80	>80 ~ 120	>120 ~ 180	>180 ~ 250	>250 ~ 315	>315 ~ 400	>400 ~ 500	
±0.12	±0.18	±0.22	±0.26	±0.31	±0.37	±0.57	±0.80	±0.93	±1.05	±1.15	±1.60	±2.20	±2.50

UL Standard		B	C	D
Rated Voltage(V)/Current(A)		300/20	/	300/10
IEC Standard				
Overvoltage Category/Pollution Degree		Ⅲ/3	Ⅲ/2	Ⅱ/2
Rated Voltage(V)/Current(A)		400/32	1000/32	/
Torque Tightening(N·m/Lb.in)		M3, 0.5/4.43		
Wire Range(rigid and flexible)(mm²/AWG)		4.0/22~12		
Pitch(mm)/Poles		8.25/N=02~26P		
Stripping length(mm)		8		
Operating temperature(°C)		-40~+105		
Conform to RoHS		Yes		



DGC825-NP10-MB361

(6=PA66)
(3=镀锡)
(B=黑色)
(M=母座)
(直脚)
(栅栏式接线端子)

3	Screw	Steel	M3/Ni Plated
2	Pin header	Copper alloy	M3/Sn Plated
1	Housing	PA66	UL94V-0
ITEM	NAME OF PART	MATERIAL	NOTES
MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES		TITLE: DG35C-C07	
DECIMALS:		PAR	DGC825-NP10-MB361
ANGLES:		DWN	
		CHKD	
		APVD	
		SCALE N:A	UNIT:MM
		SIZE:A4	SHEET:1F1
		CUSTOMER COPY	REV:A