







SPECIFICATIONS

Current Rating: 1.5 Amps
Insulation Resistance: 1000M Ω Min
Contact Resistance: 20m Ω Max
Withstanding Voltage: AC 500V
Operation Temperature: -40 $^{\circ}$ to+105 $^{\circ}$
Contact Material: Brass
Standard: PA6T
Insrlator Material: Polyester(UL 94V-0)
Contact Plating: Gold Flash
Max.Processing Temp: 240 $^{\circ}$ C for30-60seconds
(260 $^{\circ}$ C for 5 seconds)



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)

P/N	PIN	DIM.A	DIM.B
ZX-PM2.0-2-1PUW	1	0.00	2.00
ZX-PM2.0-2-2PUW	2	2.00	4.00
ZX-PM2.0-2-3PUW	3	4.00	6.00
ZX-PM2.0-2-4PUW	4	6.00	8.00
ZX-PM2.0-2-5PUW	5	8.00	10.00
ZX-PM2.0-2-6PUW	6	10.00	12.00
ZX-PM2.0-2-7PUW	7	12.00	14.00
ZX-PM2.0-2-8PUW	8	14.00	16.00
ZX-PM2.0-2-9PUW	9	16.00	18.00
.....			
ZX-PM2.0-2-40PUW	40	(PIN-1)x2.0	(PIN)x2.0

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	Yu			料号 PART NO.	ZX-PM2.0-2-NPUW	版本 REV.	A
			DECIMALS:	ANGLES:	审核 CHECK	HUANG	品名 TITLE	2.0FH H4.3 2xnPin SMT W4.5 U# PC6.5 PB4.6 6T	页次 SHEET	1/1		
			X.±0.30	X°±5°			客户料号 CUTM.NO.					
			X.X±0.20	X.X°±1°			核准 APPROVAL			RUAN		
			X.XX±0.10	X.XX°±0.5°	单位 UNITS	MM	比例 SCALE	1:1			兆星精密电子（深圳）有限公司 ShenZhen ZhaoXing Precision electronics Co., Ltd.	