




SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40°to+105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester(UL 94V-0)
Contact Plating: Gold Flash
Max.Processing Temp: 240°C for30-60seconds
(260°C for5seconds)

P/N	PIN	DIM.A	DIM.B
ZX-PM2.54-1-1PY	1	0.00	2.54
ZX-PM2.54-1-2PY	2	2.54	5.08
ZX-PM2.54-1-3PY	3	5.08	7.62
ZX-PM2.54-1-4PY	4	7.62	10.16
ZX-PM2.54-1-5PY	5	10.16	12.70
ZX-PM2.54-1-6PY	6	12.70	15.24
ZX-PM2.54-1-7PY	7	15.24	17.78
ZX-PM2.54-1-8PY	8	17.78	20.32
ZX-PM2.54-1-9PY	9	20.32	22.86
.....			
ZX-PM2.54-1-40PY	40	(PIN-1)X2.54	(PIN)X2.54



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	料号 PART NO. 品名 TITLE 客户料号 CUTM.NO.			ZX-PM2.54-1-NPY	版本 REV.	A
			DECIMALS:	ANGLES:							
			X.±0.30	X°±5°							
			X.X±0.20	X.X°±1°							
			X.XX±0.10	X.XX°±0.5°	审核 CHECK	Yu			2.54FH H8.5 1xnPin 180度 Y型 PC3.2 6T	页次 SHEET	1/1
					核准 APPROVAL	HUANG					
					单位 UNITS	RUAN					
					比例 SCALE	MM 1:1					



兆星精密电子（深圳）有限公司
ShenZhen ZhaoXing Precision electronics Co., Ltd.