







SPECIFICATIONS

Current Rating: 1.5 Amps
Insulation Resistance: 1000M Ω Min
Contact Resistance: 20m Ω Max
Withstanding Voltage: AC 500V
Operation Temperature: -40° to +105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester (UL 94V-0)
Contact Plating: Gold Flash
Max. Processing Temp: 240°C for 30-60 seconds
(260°C for 5 seconds)



P/N	PIN	DIM.A	DIM.B
ZX-PZ2.0-1-1PZZ	1	0.00	2.00
ZX-PZ2.0-1-2PZZ	2	2.00	4.00
ZX-PZ2.0-1-3PZZ	3	4.00	6.00
ZX-PZ2.0-1-4PZZ	4	6.00	8.00
ZX-PZ2.0-1-5PZZ	5	8.00	10.00
ZX-PZ2.0-1-6PZZ	6	10.00	12.00
ZX-PZ2.0-1-7PZZ	7	12.00	14.00
ZX-PZ2.0-1-8PZZ	8	14.00	16.00
ZX-PZ2.0-1-9PZZ	9	16.00	18.00
.....			
ZX-PZ2.0-1-40PZZ	40	(PIN-1)x2.0	(PIN)x2.0



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE: ±0.05 (TOP VIEW)

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	料号 PART NO.	版本 REV.	A
			DECIMALS:	ANGLES:	审核 CHECK	品名 TITLE	页次 SHEET	1/1
			X.±0.30	X°±5°	核准 APPROVAL	客户料号 CUTM.NO.		
			X.X±0.25	X.X°±1°				
			X.XX±0.20	X.XX°±0.5°	单位 UNITS	兆星精密电子(深圳)有限公司 ShenZhen ZhaoXing Precision electronics Co., Ltd.		
					MM	比例 SCALE	1:1	