







SPECIFICATIONS

Current Rating: 1.5 Amps
Insulation Resistance: 1000M Ω Min
Contact Resistance: 20m Ω Max
Withstanding Voltage: AC 500V
Operation Temperature: -40° to +105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester (UL 94V-0)
Contact Plating: Gold Flash
Max. Processing Temp: 240°C for 30-60 seconds
(260°C for 5 seconds)

P/N	PIN	DIM.A	DIM.B
ZX-PZ2.0-2-1PZZ	2*1	0.00	2.00
ZX-PZ2.0-2-2PZZ	2*2	2.00	4.00
ZX-PZ2.0-2-3PZZ	2*3	4.00	6.00
ZX-PZ2.0-2-4PZZ	2*4	6.00	8.00
ZX-PZ2.0-2-5PZZ	2*5	8.00	10.00
ZX-PZ2.0-2-6PZZ	2*6	10.00	12.00
ZX-PZ2.0-2-7PZZ	2*7	12.00	14.00
ZX-PZ2.0-2-8PZZ	2*8	14.00	16.00
ZX-PZ2.0-2-9PZZ	2*9	16.00	18.00
.....			
ZX-PZ2.0-2-40PZZ	2*40	(PIN-1)x2.0	(PIN)x2.0



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE: ± 0.05 (TOP VIEW)

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	料号 PART NO.			版本 REV.	A
			DECIMALS:	ANGLES:	审核 CHECK	Yu			品名 TITLE	1/1
			X. ± 0.30	X° $\pm 5^\circ$	核准 APPROVAL	HUANG			2.0PH H2.0 2xPin 180 μ PC2.8 PA3.9 PB2.0 L8.7 6T	
			X.X ± 0.25	X.X° $\pm 1^\circ$		RUAN			客户料号 CUTM.NO.	
			X.XX ± 0.20	X.XX° $\pm 0.5^\circ$	单位 UNITS	MM	比例 SCALE	1:1	兆星精密电子(深圳)有限公司 ShenZhen ZhaoXing Precision electronics Co., Ltd.	