








SPECIFICATIONS

Current Rating: 1.5 Amps
Insulation Resistance: 1000M Ω Min
Contact Resistance: 20m Ω Max
Withstanding Voltage: AC 500V
Operation Temperature: -40° to +105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester (UL 94V-0)
Contact Plating: Gold Flash
Max. Processing Temp: 240°C for 30-60 seconds
(260°C for 5 seconds)

P/N	PIN	DIM.A	DIM.B
BX-PZ2.0-2-1PZZ	2*1	0.00	2.00
BX-PZ2.0-2-2PZZ	2*2	2.00	4.00
BX-PZ2.0-2-3PZZ	2*3	4.00	6.00
BX-PZ2.0-2-4PZZ	2*4	6.00	8.00
BX-PZ2.0-2-5PZZ	2*5	8.00	10.00
BX-PZ2.0-2-6PZZ	2*6	10.00	12.00
BX-PZ2.0-2-7PZZ	2*7	12.00	14.00
BX-PZ2.0-2-8PZZ	2*8	14.00	16.00
BX-PZ2.0-2-9PZZ	2*9	16.00	18.00
.....			
BX-PZ2.0-2-40PZZ	2*40	(PIN-1)x2.0	(PIN)x2.0



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE: ± 0.05 (TOP VIEW)

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	Yu			料号 PART NO.	BX-PZ2.0-2-NPZZ		版本 REV.	A
			DECIMALS:	ANGLES:	审核 CHECK	HUANG	品名 TITLE	2.0PH H2.0 2xPin 180# PC2.8 PA3.9 PB2.0 L8.7 6T		页次 SHEET	1/1		
			X.±0.30	X°±5°	核准 APPROVAL		客户料号 CUTM.NO.						
			X.X±0.25	X.X°±1°									
			X.XX±0.20	X.XX°±0.5°	单位 UNITS	MM	比例 SCALE	1:1	 Bossie (博锡)				