






SPECIFICATIONS

Current Rating: 1.5 Amps
Insulation Resistance: 1000M Ω Min
Contact Resistance: 20m Ω Max
Withstanding Voltage: AC 500V
Operation Temperature: -40 $^{\circ}$ to+105 $^{\circ}$
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester(UL 94V-0)
Contact Plating: Gold Flash
Max.Processing Temp: 240 $^{\circ}$ C for30-60seconds
(260 $^{\circ}$ C for 5 seconds)



P/N	PIN	DIM.A	DIM.B
BX-PM2.0-1-1PY	1	0.00	2.00
BX-PM2.0-1-2PY	2	2.00	4.00
BX-PM2.0-1-3PY	3	4.00	6.00
BX-PM2.0-1-4PY	4	6.00	8.00
BX-PM2.0-1-5PY	5	8.00	10.00
BX-PM2.0-1-6PY	6	10.00	12.00
BX-PM2.0-1-7PY	7	12.00	14.00
BX-PM2.0-1-8PY	8	14.00	16.00
BX-PM2.0-1-9PY	9	16.00	18.00
.....			
BX-PM2.0-1-40PY	40	(PIN-1)x2.0	(PIN)x2.0



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	Yu			料号 PART NO.	BX-PM2.0-1-NPY	版本 REV.	A
			DECIMALS:	ANGLES:	审核 CHECK	HUANG			品名 TITLE	2.0FH H4.3 1xnPin 180# W2.4 U# PC2.8 6T	页次 SHEET	1/1
			X.±0.30	X°±5°	核准 APPROVAL	RUAN			客户料号 CUTM.NO.			
			X.X±0.20	X.X°±1°	单位 UNITS	MM	比例 SCALE	1:1	Bossie (博锡)			
			X.XX±0.10	X.XX°±0.5°								