







SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40°to +105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester(UL 94V-0)
Contact Plating: Gold Flash
Max.Processing Temp: 240°C for 30-60seconds
(260°C for 5seconds)



P/N	PIN	DIM.A	DIM.B
ZX-PM2.54-2- 1PY	1	0.00	2.54
ZX-PM2.54-2- 2PY	2	2.54	5.08
ZX-PM2.54-2- 3PY	3	5.08	7.62
ZX-PM2.54-2- 4PY	4	7.62	10.16
ZX-PM2.54-2- 5PY	5	10.16	12.70
ZX-PM2.54-2- 6PY	6	12.70	15.24
ZX-PM2.54-2- 7PY	7	15.24	17.78
ZX-PM2.54-2- 8PY	8	17.78	20.32
ZX-PM2.54-2- 9PY	9	20.32	22.86
.....			
ZX-PM2.54-2-40PY	40	(PIN-1)X2.54	(PIN)X2.54

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	料号 PART NO.			版本 REV.	A
			DECIMALS:	ANGLES:	审核 CHECK	Yu			品名 TITLE	页次 SHEET
			X.X±0.30	X°±5°	核准 APPROVAL	HUANG			2.54FH H8.5 2xPin 180# Y# PC3.2 6T	1/1
			X.X±0.20	X.X°±1°		RUAN			客户料号 CUTM.NO.	
			X.XX±0.10	X.XX°±0.5°	单位 UNITS	MM	比例 SCALE	1:1	兆星精密电子（深圳）有限公司 ShenZhen ZhaoXing Precision electronics Co., Ltd.	