







SPECIFICATIONS

Current Rating: 1.5 Amps
 Insulation Resistance: 1000M Ω Min
 Contact Resistance: 20m Ω Max
 Withstanding Voltage: AC 500V
 Operation Temperature: -40° to +105°
 Contact Material: Brass
 Standard: PA6T
 Insulator Material: Polyester (UL 94V-0)
 Contact Plating: Gold Flash
 Max. Processing Temp: 240°C for 30-60 seconds
 (260°C for 5 seconds)



P/N	PIN	DIM.A	DIM.B
BX-PZ2.0-1-1PZZ	1	0.00	2.00
BX-PZ2.0-1-2PZZ	2	2.00	4.00
BX-PZ2.0-1-3PZZ	3	4.00	6.00
BX-PZ2.0-1-4PZZ	4	6.00	8.00
BX-PZ2.0-1-5PZZ	5	8.00	10.00
BX-PZ2.0-1-6PZZ	6	10.00	12.00
BX-PZ2.0-1-7PZZ	7	12.00	14.00
BX-PZ2.0-1-8PZZ	8	14.00	16.00
BX-PZ2.0-1-9PZZ	9	16.00	18.00
.....			
BX-PZ2.0-1-40PZZ	40	(PIN-1)x2.0	(PIN)x2.0



RECOMMEND P.C.B LAYOUT
 PCB TOLERANCE: ± 0.05 (TOP VIEW)

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	Yu		料号 PART NO.	BX-PZ2.0-1-NPZZ	版本 REV.	A
			DECIMALS:	ANGLES:	审核 CHECK	HUANG		品名 TITLE	2.0PH H2.0 1xPin 180 μ PC2.8 PA3.9 PB2.0 L8.7 6T	页次 SHEET	1/1
			X. ± 0.30	X° $\pm 5^\circ$	批准 APPROVAL	RUAN		客户料号 CUTM.NO.			
			X.X ± 0.25	X.X° $\pm 1^\circ$	单位 UNITS	MM	比例 SCALE	1:1			
			X.XX ± 0.20	X.XX° $\pm 0.5^\circ$							