


SPECIFICATIONS

Current Rating: 1.5 Amps
Insulation Resistance: 1000M Ω Min
Contact Resistance: 20m Ω Max
Withstanding Voltage: AC 500V
Operation Temperature: -40° to +105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester (UL 94V-0)
Contact Plating: Gold Flash
Max. Processing Temp: 240°C for 30-60 seconds
(260°C for 5 seconds)

P/N	PIN	DIM.A	DIM.B
PZ2.0-UP1D-01A	1	0.00	2.00
PZ2.0-UP1D-02A	2	2.00	4.00
PZ2.0-UP1D-03A	3	4.00	6.00
PZ2.0-UP1D-04A	4	6.00	8.00
PZ2.0-UP1D-05A	5	8.00	10.00
PZ2.0-UP1D-06A	6	10.00	12.00
PZ2.0-UP1D-07A	7	12.00	14.00
PZ2.0-UP1D-08A	8	14.00	16.00
PZ2.0-UP1D-09A	9	16.00	18.00
.....			
PZ2.0-UP1D-40A	40	(PIN-1)x2.0	(PIN)x2.0



DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.50	X.*± 5°	APR.	Alex	TITLE: 2.0PH H2.0 1xnPin 180μ PC2.8 PA3.9 PB2.0 L8.7 6T	
.XX±0.20	.X.*± 3°	CHK.	Jack	DWG NO. PZ2.0-UP1D-NA	
.XXX±0.10	.XX*± 1°	DRA.	Can	PROJ.	CUSTOMER DRAWING
				SIZE A4	SCALE 1:1