




SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000M Ω Min
Contact Resistance: 20m Ω Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40° to +105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester(UL 94V-0)
Contact Plating: Gold Flash
Max.Processing Temp: 240°C for 30-60seconds
(260°C for 5seconds)

P/N	PIN	DIM.A	DIM.B
PZ2.54-WA2D-01A	1	0.00	2.54
PZ2.54-WA2D-02A	2	2.54	5.08
PZ2.54-WA2D-03A	3	5.08	7.62
PZ2.54-WA2D-04A	4	7.62	10.16
PZ2.54-WA2D-05A	5	10.16	12.70
PZ2.54-WA2D-06A	6	12.70	15.24
PZ2.54-WA2D-07A	7	15.24	17.78
PZ2.54-WA2D-08A	8	17.78	20.32
PZ2.54-WA2D-09A	9	20.32	22.86
.....			
PZ2.54-WA2D-40A	40	(PIN-1)X2.54	(PIN)X2.54



DIMENSION in mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.50	X.*± 5°	APR. Alex	TITLE: 2.54PH H2.5 1xnPin 90度 PC3.0 PA6.0 PB4.3 L13.8 6T 铜面		
.XX±0.20	.X.*± 3°	CHK. Jack	DWG NO. PZ2.54-WA2D-NA		
.XXX±0.10	.XX.*± 1°	DRA. Can	PROJ. 		CUSTOMER DRAWING
			SIZE A4	SCALE 1:1	SHEET 1/3