





SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40° to +105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester(UL 94V-0)
Contact Plating: Gold Flash
Max.Processing Temp: 240°C for 30-60seconds
(260°C for 5seconds)

P/N	PIN	DIM.A	DIM.B
PZ2.54-WA2S-01A	2*1	0.00	2.54
PZ2.54-WA2S-02A	2*2	2.54	5.08
PZ2.54-WA2S-03A	2*3	5.08	7.62
PZ2.54-WA2S-04A	2*4	7.62	10.16
PZ2.54-WA2S-05A	2*5	10.16	12.70
PZ2.54-WA2S-06A	2*6	12.70	15.24
PZ2.54-WA2S-07A	2*7	15.24	17.78
PZ2.54-WA2S-08A	2*8	17.78	20.32
PZ2.54-WA2S-09A	2*9	20.32	22.86
.....			
PZ2.54-WA2S-40A	2*40	(PIN-1)X2.54	(PIN)X2.54



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE: ±0.05 (TOP VIEW)

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	Alex	TITLE: 2.54PH H2.5 2xPin 90° PC3.0 PA6.0 PB6.9 L13.8/18.8 6T 特制	
.X±0.50	.X*± 5°	CHK.	Jack	DWG NO. PZ2.54-WA2S-NA	
.XX±0.20	.X*± 3°	DRA.	Can	CUSTOMER DRAWING	
.XXX±0.10	.XX*± 1°	PROJ.		SIZE A4	SCALE 1:1
				SHEET 1/3	REV. A