





P/N	PIN	DIM.A	DIM.B
PM2.54-YD2D-01A	1	0.00	2.54
PM2.54-YD2D-02A	2	2.54	5.08
PM2.54-YD2D-03A	3	5.08	7.62
PM2.54-YD2D-04A	4	7.62	10.16
PM2.54-YD2D-05A	5	10.16	12.70
PM2.54-YD2D-06A	6	12.70	15.24
PM2.54-YD2D-07A	7	15.24	17.78
PM2.54-YD2D-08A	8	17.78	20.32
PM2.54-YD2D-09A	9	20.32	22.86
.....			
PM2.54-YD2D-40A	40	(PIN-1)X2.54	(PIN)X2.54

SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40°to+105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester(UL 94V-0)
Contact Plating: Gold Flash
Max.Processing Temp: 240°C for30-60seconds
(260°C for5seconds)



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.50	X.*± 5°	APR. Alex	TITLE: 2.54FH H8.5 1xnPin 90度 Y型 PC3.2 PB10.2 6T		
.XX±0.20	.X.*± 3°	CHK. Jack	DWG NO. PM2.54-YD2D-NA		
.XXX±0.10	.XX*± 1°	DRA. Can	PROJ. 		CUSTOMER DRAWING
			SIZE A4	SCALE 1:1	SHEET 1/3