




REV	LTR	DESCRIPTION	DATE	APPROVED



NOTE:

1. 材质

1.1. 塑胶: PBT白胶/黑胶/蓝胶/透明

1.2. 端子: C2680R-H T=0.25±0.01

1.3. 外壳: SPCC T=0.30±0.01

1.4. 中夹片: SPCC T=0.30±0.01

2. 机械性能:

插拔力: 插入力 35N MAX ,

拔出力 10N MIN



机械寿命: 插拔1500次

3. 端子:

打镍底50~80u", 焊脚镀锡80~120u",

接触区镀金1u"

4. 外壳: 镀镍



TOLERANCES	
.X	±0.30
.XX	±0.20
.XXX	±0.10
ANGLES	±2.00°

深圳市连欣科技有限公司

APPROVED: 奉 卿	TITLE: 0	USB AF 双层10.5mm有边
CHECKED: 肖解红	PART NO.: XUDF-0208-1051	PROJECTION:
DRAWING:	REV.: A/0	SIZE: A4
	UNIT: M M	SCALE: 1:1
		SHEET: 1/1