











7		8	
REV.	REVISION DESCRIPTION	DATE	APPD



技术要求 (Technical requirements) :

1. 材质 (material): 黄铜 (brass)
2. 材料规格 (Material specifications): 0.4mm
3. 压线范围 (Wire): AWG14#--10#
4. 表面处理 (Surface treatment): 锡 (Tin plated)
5. 额定电压 Rated voltage : 300V AC.DC.
6. 额定电流 Rated current : 15A AC.DC.
7. 接触电阻 Contact resistance: 20mΩ MAX
8. 绝缘电阻 Insulation resistance: 1000 MΩ MIN
9. 耐压 Withstand voltage: 2000V AC/minute
10. 配0.5/0.8mm插片

GENERAL TOLERANCES (UNLESS SPECIFIED)		浙江德利接插件有限公司 ZHE JIANG DELI CONNECTORS CO., LTD			
.X: ±0.25	X°: ±3.0°	PRODUCT NAME: DL250ZCGJ		TITLE: 250 Sheath Series	
.XX: ±0.15	.X°: ±2.0°				
.XXX: ±0.01	.XX°: ±1.0°	DR.: Chen Quan Long	DATE.: 21.04.11	PART. NO.:	
FINISH: _____		CHKD.: Wu Hui	DATE.: 21.04.11		
DRAWING NO.:		APPD.: Ren An De	DATE.: 21.04.11	SCALE: N/A	PAGE: 1/1
				UNITS: mm	REV.: A

1 2 3 4 5 6 7 8

A


B

C


D

E

F



C向



技术要求 (Technical requirements) :

1. 材质 (material): 黄铜 (brass)
2. 材料规格 (Material specifications) : 0.4mm
3. 压线范围 (Wire) : 低脚: AWG22#--18#/中脚: AWG18#--14#
高脚: AWG14#--10#
4. 表面处理 (Surface treatment) : 镀锡
5. 额定电压Rated voltage : 300V AC.DC.
6. 额定电流Rated current : 15A AC.DC.
7. 接触电阻Contact resistance: 20mΩ MAX
8. 绝缘电阻Insulation resistance: 1000 MΩ MIN
9. 耐压Withstand voltage: 2000V AC/minute
10. 配0.5/0.8mm插片

A


B

C


D

E



F



A-A



B-B







Product name		Dimension mm			
		A1	B1	A2	B2
DL250ZCDSJ	DLS25021	5.0	4.8	2.9	3.1
DL250ZCDSZJ	DLS25022	5.1	5.5	3.7	3.7
DL250ZCDSGJ	DLS25023	5.8	6.5	4	5.4

GENERAL TOLERANCES (UNLESS SPECIFIED)		浙江德利接插件有限公司 ZHEJIANG DELI CONNECTORS CO.,LTD			
.X: ±0.25	.X°: ±3.0°	PRODUCT NAME: DL250ZCDSxx		TITLE: 250 Sheath Series	
.XX: ±0.15	.X°: ±2.0°	DR.: Chen Quan Long	DATE.:21.04.1	PART. NO.:	
.XXX: ±0.01	.XX°: ±1.0°	CHKD.:Wu Hui	DATE.:21.04.1	SCALE: N/A	PAGE: 1/1
FINISH: —		APPD.:Ren An De	DATE.:21.04.1	UNITS: mm	REV.: A
DRAWING NO.:					


B	新模统一长度与宽度尺寸	24.3.22	WH
REV.	REVISION DESCRIPTION	DATE	APPD





1 2 3 4 5 6 7 8



技术要求 (Technical requirements) :


1. 材质 (material): 黄铜 (brass)
2. 材料规格 (Material specifications): 0.45mm
3. 压线范围 (Wire): AWG18#--14#
4. 表面处理 (Surface treatment): 哑光 (Matte plated)
5. 额定电压 Rated voltage : 300V AC.DC.
6. 额定电流 Rated current : 15A AC.DC.
7. 接触电阻 Contact resistance: 20mΩ MAX
8. 绝缘电阻 Insulation resistance: 1000 MΩ MIN
9. 耐压 Withstand voltage: 2000V AC/minute
10. 配0.5/0.8mm插片

GENERAL TOLERANCES (UNLESS SPECIFIED)		浙江德利接插件有限公司 ZHEJIANG DELI CONNECTORS CO.,LTD			
.X: ±0.25	X° : ±3.0°	PRODUCT NAME: DL250QX		TITLE: 250	
.XX: ±0.15	.X° : ±2.0°	DR.:Chen Quan Long		DATE.:20.04.1	
.XXX: ±0.01	.XX° : ±1.0°	CHKD.:Wu Hui		DATE.:20.04.1	
FINISH: _____		APPD.:Ren An De		DATE.:20.04.1	
DRAWING NO.:		UNITS: mm		REV. : A	




技术要求 (Technical requirements) :

1. 材质 (material): 黄铜 (brass)
2. 材料规格 (Material specifications) : 0.4mm
3. 压线范围 (Wire) : AWG18#--14#
4. 表面处理 (Surface treatment) : 镀锡 (tin plated)
5. 额定电压 Rated voltage : 300V AC.DC.
6. 额定电流 Rated current : 15A AC.DC.
7. 接触电阻 Contact resistance: 20mΩ MAX
8. 绝缘电阻 Insulation resistance: 1000 MΩ MIN
9. 耐压 Withstand voltage: 2000V AC/minute
10. 配0.5/0.8mm插片

GENERAL TOLERANCES (UNLESS SPECIFIED)		浙江德利接插件有限公司 ZHEJIANG DELI CONNECTORS CO.,LTD			
.X: ±0.25	X° : ±3.0°	PRODUCT NAME: DL250QXDS		TITLE: 250	
.XX: ±0.15	.X° : ±2.0°	DR.:Chen Quan Long		PART NO. :	
.XXX: ±0.01	.XX° : ±1.0°	DATE. :20.04.1			
FINISH: _____		CHKD.:Wu Hui		SCALE: N/A	
		DATE. :20.04.1		PAGE: 1/1	
DRAWING NO. :		APPD.:Ren An De		UNITS: mm	
		DATE. :20.04.1		REV. : A	

REV.	ECN. NO.	REVISION DESCRIPTION	DATE	APPD




7		8	
REV.	REVISION DESCRIPTION	DATE	APPD

技术要求 (Technical requirements) :


1. 材质 (material): 黄铜 (brass)
2. 材料规格 (Material specifications): 0.4mm
3. 压线范围 (Wire): AWG20#--16#
4. 表面处理 (Surface treatment): 哑光 (Matte plated)
5. 额定电压 Rated voltage: 300V AC.DC.
6. 额定电流 Rated current: 15A AC.DC.
7. 接触电阻 Contact resistance: 20mΩ MAX
8. 绝缘电阻 Insulation resistance: 1000 MΩ MIN
9. 耐压 Withstand voltage: 2000V AC/minute
10. 配 0.5/0.8mm 插片

GENERAL TOLERANCES (UNLESS SPECIFIED)		浙江德利接插件有限公司	
. X: ±0.25		ZHEJIANG DELI CONNECTORS CO.,LTD	
. XX: ±0.15	X°: ±3.0°	PRODUCT NAME: DL250QXSB	TITLE: 250
. XXX: ±0.01	. X°: ±2.0°	DR.: Chen Quan Long	DATE.: 21.05.05
FINISH:	. XX°: ±1.0°	DATE.: 21.05.05	PART. NO.:
		CHKD.: Wu Hui	SCALE: N/A
DRAWING NO.:		DATE.: 21.05.05	PAGE: 1/1
		APPD.: Ren An De	UNITS: mm
			REV.: A




REV.	REVISION DESCRIPTION	DATE	APPD




C向



D向旋转



A-A




B-B

技术要求 (Technical requirements) :

1. 材质 (material): 黄铜 (brass)
2. 材料规格 (Material specifications): 0.4mm
3. 压线范围 (Wire): AWG18#--14#
4. 表面处理 (Surface treatment): 锡 (Tin plated)
5. 额定电压 Rated voltage: 300V AC.DC.
6. 额定电流 Rated current: 15A AC.DC.
7. 接触电阻 Contact resistance: 20mΩ MAX
8. 绝缘电阻 Insulation resistance: 1000 MΩ MIN
9. 耐压 Withstand voltage: 2000V AC/minute
10. 配0.8mm插片

GENERAL TOLERANCES (UNLESS SPECIFIED)		浙江德利接插件有限公司 ZHE JIANG DELI CONNECTORS CO.,LTD	
. X: ±0.25	. X° : ±3.0°	PRODUCT NAME: DL250ZCJB	TITLE: 250 Sheath Series
. XX: ±0.15	. XX° : ±2.0°	DR.: Chen Quan Long	DATE.: 21.04.11
. XXX: ±0.01	. XXX° : ±1.0°	CHKD.: Wu Hui	DATE.: 21.04.11
FINISH:		APPD.: Ren An De	DATE.: 21.04.11
DRAWING NO.:			



技术参数(SPECIFICATIONS)

额定电压 (Voltage rating): 300V, AC, DC

额定电流 (Current rating): 15A

接触电阻 (Contact resistance): $\leq 0.02 \Omega$


绝缘电阻 Insulation resistance: $1000 M\Omega$ MIN

材质 (material): 黄铜 (brass)

材料规格 (Material specifications): 0.5mm/0.8mm

表面处理 (Surface treatment): 镍底镀锡 (Nickel bottom tin)

GENERAL TOLERANCES (UNLESS SPECIFIED)		浙江德利接插件有限公司 ZHEJIANG DELI CONNECTORS CO.,LTD			
.X: ± 0.25	.X°: $\pm 3.0^\circ$	PRODUCT NAME: DL2500122ST		TITLE: 250	
.XX: ± 0.15	.XX°: $\pm 2.0^\circ$			PART. NO.:	
.XXX: ± 0.01	.XXX°: $\pm 1.0^\circ$	DR.: Chen Quan Long	DATE.: 20.04.01	SCALE: N/A	
FINISH:		CHKD.: Wu Hui	DATE.: 20.04.01	PAGE: 1/1	
DRAWING NO:		APPD.: Ren An De	DATE.: 20.04.01	UNITS: mm	REV.: A



技术要求 (Technical requirements) :

额定电压Rated voltage :300V AC.DC.

额定电流Rated current :15A AC.DC.

接触电阻Contact resistance:20MΩ MAX


绝缘电阻Insulation resistance: 1000 MΩ MIN

材质 (material): 黄铜 (brass)

材料规格 (Material specifications) : 0.8/0.5mm

表面处理 (Surfacetreatment) : 镍底镀锡 (Nickel bottom tin)

GENERAL TOLERANCES (UNLESS SPECIFIED)		浙江德利接插件有限公司 ZHEJIANG DELI CONNECTORS CO.,LTD	
. X: ±0.25	X° : ±3.0°	PRODUCT NAME: DL2500222ST	TITLE: 250
. XX: ±0.15	. X° : ±2.0°		
. XXX: ±0.01	. XX° : ±1.0°	DR.:Chen Quan Long	DATE.:21.11.08
FINISH:		CHKD.:Wu Hui	DATE.:21.11.08
DRAWING NO.:		APPD.:Ren An De	DATE.:21.11.08
		SCALE: N/A	PAGE: 1/1
		UNITS: mm	REV.: A





REV.	REVISION DESCRIPTION	DATE	APPD

技术参数 (SPECIFICATIONS)

温度范围 (Temperature range): $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$
额定电压 (Voltage rating): 300V, AC, DC
额定电流 (Current rating): 15A
接触电阻 (Contact resistance): $\leq 20\text{m}\Omega$
绝缘电阻 (Insulation resistance): 常温 $\geq 1000\text{M}\Omega$
材料 (Material): 壳体 (Housing): 尼龙


GENERAL TOLERANCES (UNLESS SPECIFIED)		浙江德利接插件有限公司			
.X: ± 0.25	X° : $\pm 3.0^{\circ}$	PRODUCT NAME: DL250ZCYHT		TITLE: 250 Housing	
.XX: ± 0.15	.X° : $\pm 2.0^{\circ}$			PART NO:	
.XXX: ± 0.01	.XX° : $\pm 1.0^{\circ}$	DR:Chen Quan Long	DATE:19/12/15	SCALE: N/A PAGE: 1/1	
FINISH:		CHKD: Wu Hui	DATE:19/12/15		
DRAWING NO:		APPD:Ren An De	DATE:19/12/15	UNITS: mm	REV. : A





REV.	REVISION DESCRIPTION	DATE	APPD

GENERAL TOLERANCES (UNLESS SPECIFIED)				ZHE JIANG DELI CONNECTORS CO ., LTD			
. X: ± 0.25	X° : ± 3.0°	PRODUCT NAME:		TITLE:			
. XX: ± 0.15	. X° : ± 2.0°	DL250QXRHT					
. XXX: ± 0.01	. XX° : ± 1.0°	DR: Chen Quan Long	DATE: 21/11/23	PART NO:			
FINISH:		DR: Wu Hui	DATE: 21/11/23	SCALE: N/A		PAGE: 1/1	
DRAWING NO:		APPD: Ren An De	DATE: 21/11/23	UNITS: mm		REV. : A	



REV.	REVISION DESCRIPTION	DATE	APPD

技术参数 (SPECIFICATIONS)

温度范围 (Temperature range): $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$

额定电压 (Voltage rating): 300V, AC, DC

额定电流 (Current rating): 15A

接触电阻 (Contact resistance): $\leq 10\text{M}\Omega$

绝缘电阻 (Insulation resistance): 常温 $\geq 1000\text{M}\Omega$

材料 (Material): 壳体 (Housing): Nylon UL94V-0(2)

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO., LTD			
.X: ± 0.25	X°: $\pm 3.0^{\circ}$	PRODUCT NAME: DL250QXYHT		TITLE: 250 Sheath Series	
.XX: ± 0.15	.X°: $\pm 2.0^{\circ}$	DR: Chen Quan Long		DATE: 19/07/01	
.XXX: ± 0.01	.XX°: $\pm 1.0^{\circ}$	CHKD: Wu Hui		DATE: 19/07/01	
FINISH: _____		APPD: Ren An De		DATE: 19/07/01	
DRAWING NO: _____		SCALE: N/A		PAGE: 1/1	REV.: A