





SECTION C-C

■ Specification :


- 1. Rating:
Voltage :12V AC/DC max., 2V DC min.
Current: 10mA AC/DC max., 10μA DC min.
- 2. Contact Resistance : 100mΩ Max
- 3. Insulation Resistance : 100MΩ at 500V
- 4. Withstand Voltage : AC100V (50-60Hz)
for 1 minute
- 5. Mating Force : 3.0kgf max
- 6. Operating Life : 5000 Cycles



SECTION A-A



RECOMMENDED PCB LAYOUT
TOLERANCE:±0.05mm



SECTION B-B

_____		new		2015/5/3		A		瀚源	
ECN BO.		DESCRIPTION.		DATE.		REV.			
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER			SCALT: 1/2		SCALE: 3:1	
Mikey	Tom	Jerry	PART NAME	CPG151101S11-2	UNLESS OTHERWISE SPECIFIED,TOLERANCE:		X. ±0.25		
			MODEL NAME	CPG151101S11-2			X.x ±0.20		
			3RD ANGLE PROJ			HanElectricity Co.,LTD			