







3D VIEW



(ø3.50mm 4 POLE PLUG)



1. CONTACT CURRENT RATING: 1A.
2. CONTACT RESISTANCE: 100 mΩ MAX.;
3. INSULATION RESISTANCE: 100MΩ MIN.;
4. DIELECTRIC WITHSTANDING: 500V AC MIN.;
5. DURABILITY: 5,000 CYCLES MIN.;
6. CONNECTOR MATING FORCES: 30N MAX.;
7. CONNECTOR UNMATING FORCES: 3N MIN.;
8. TERPROOF LEVEL: IPX7;



P.C.B LAYOUT(TOP view)

③	Waterproof ring	——	1	Silica gel	——	——
②	Terminal	——	5	Phosphor bronze/SUS	Ni Plating	——
①	Housing	——	1	HTP	Black	——
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
APPROVALS			DATE	 hro [®]		
DRAWN	LIUCAN	2021.04.27				
CHECKED						
APPROVALS						
				TITLE:	PHONE JACKS	
				PART NO.	PJ-621B	
TOLERANCES ARE		30~以上 ±0.30 10~30 ±0.20 5~10 ±0.15 ~ 5 ±0.10	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 
			±2'	DRAWING NO.	——	SHEET 1 OF

_____	A	_____	NEW	_____	_____	_____
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.