



A

B








C

D

E



AFTER MATING

RECOMMENDED PCB LAYOUT
TOLERANCE:±0.05SCALE: UNIT: mm
SIZE: A4Unless otherwise
General Tolerance:
X. ±0.25
X.x ±0.20
X.xx ±0.15
X.xxx ±0.10
X° ±5°Title: Horizontal Type-c 16P Female
Pad up 4.3 CH=5.9 L=8.0mm

Molde Code: GT-USB-7016

DRAWN: Xla
CHECKED: Chen
APPROVED: Chen
DATE:品赞科技®
b-Switch
www.dg-switch.com

REV: A0

SHEET: 1/1

1	HOUSING	HIGH TEMPERATURE PLASTIC	BLACK UL 94 V-0
2	CONTACT	COPPER ALLOY	Au PLATING ON CONTACT AREA
3	SHIELDING PLATE	STAINLESS STEEL	CLEAN
4	INNER SHELL	STAINLESS STEEL	Ni MIN PLATED
5	OUTER SHELL	STAINLESS STEEL	Ni MIN PLATED
NO.	PARTS	MATERIAL	REMARKS

RoHS
Compliant
EU RoHS Standards

A

B

C

D

E