




▲ Non-tooled parts
NO.of positions DIM list:

CONTACTS	DIMENSIONS	
	A	B
4	2.54	5.48
6	5.08	8.02
8	7.62	10.56
10	10.16	13.10
12	12.70	15.64
14	15.24	18.18
16	17.78	20.72
18	20.32	23.26
20	22.86	25.80
22	25.40	28.34
24	27.94	30.88
26	30.48	33.42
28	33.02	35.96
30	35.56	38.50
32	38.10	41.04
34	40.64	43.58
36	43.18	46.12
38	45.72	48.66
40	48.26	51.20
42	50.80	53.74
44	53.34	56.28
46	55.88	58.82
48	58.42	61.36
50	60.96	63.90
52	63.50	66.44
54	66.04	68.98
56	68.58	71.52
58	71.12	74.06
60	73.66	76.60
62	76.20	79.14
64	78.74	81.68
66	81.28	84.22
68	83.82	86.76
70	86.36	89.30
72	88.90	91.84
74	91.44	94.38
76	93.98	96.92
78	96.52	99.46
80	99.06	102.00

1,ELECTRICAL SPECIFICATIONS:

- 1.1 Rated current(额定电流):
3A
- 1.2 Dielectric Withstanding Voltage(耐电压) :
1000V AC for one minute
- 1.3 Contact Resistance(接触电阻) :
<20mΩ
- 1.4 Insulation Resistance(绝缘电阻) :
>1000MΩ
- 1.5 Operating Temperature(工作温度) :
-40℃ ~ 105℃

2,MATERIAL SPECIFICATION:

- 2.1 Insulator Material(绝缘体材质):
High Temperature Plastic ,
UL94V-0
- 2.2 Contact Material(端子材质):
Brass

PART NO. LEGEND:

FP 6 Q XX S -X 1 U 32-X

Female Header

Pitch:6=2.54mm

Plastic Height: Q=8.50mm

NO of Contacts: 4 to 80

Packing: C:TUBE
B:TRAY

Contact Plating : 1;G/F

Insulator Material: B:PA6T
C:PA9T

Series No: S

DRAWING:
Hu yatao

CHECKED:
Tony

APPROVAL:
Yang jie

GENERAL TOLERANCE


.X:=±0.30 .X*:=±2°
.XX:=±0.20 .XX*:=±1°
.XXX:=±0.10 .XXX*:=±0.5°

UNIT: MM

SCALE: N/A

SHEET: 1/1

PROJECTION:



CHIN-BAN
electronics (H.K.) co., ltd

DESCRIPTION:
2.54mm Pitch Female Header Double Row DIP180°

PART NO: FP6QXXS-X1U32-X

REV:1.0

CUSTOMER NO:

SIZE: A4