






RoHS2.0+REACH

NO.	COMPONENTS	MATERIALS	SPECIFICATION:FINISH/COLOR	QTY.
1	HOUSING	PBT UL94V-0	BLACK	1



NOTE(UNLESS OTHERWISE SPECIFIED):
1. ALL MATERIAL MUST BE COMPLY WITH ROHS+REACH.
2. PRODUCT PERFORMANCE:
2.1 RATED VOLTAGE(MAX.):250V AC/DC
2.2 RATED CURRENT(MAX.):7.0A AC/DC (24AWG)
2.3 DIELECTRIC STRENGTH:1500V AC/MINUTE
2.4 INSULATION RESISTANCE:1000 MΩ MIN.
2.5 CONTACT RESISTANCE:10 mΩ MAX.
2.6 OPERATING TEMPERATURE:-55°C TO +105°C
3.APPLICABLE WIRE: CONDUCTOR SIZE/ AWG #24 TO #28
INSULATION O.D./ 0.8 TO 1.4mm
4.PART NO. : 3GY01- R39006-A2001

WATER CODE
006:6PIN

DRAWING:
ShunMingWen

CHECKED:
TianHai

APPROVAL:
Cykin


GENERAL TOLERANCE
.X:=±0.30 .X°:=±2°
.XX:=±0.20 .XX°:=±1°
.XXX:=±0.10 .XXX°:=±0.5°

UNIT: MM

SCALE: 1:1

SHEET: 1/1

PROJECTION:



CHIN-BAN
Electronic Technology

DESCRIPTION: 2*3PIN INLINE HOUSING-DOUBLE(3.81mm PITCH)

PART NO: 3GY01-R39006-A2001

OLD CODE:

DRAWING NO: UK0680

REV: 1.0

SIZE: A4

2.0			
1.0	09/25.24	NEW	ShunMingWen
NO.	DATE	DESCRIPTION	DRAWING