






RoHS

NO.	COMPONENTS	MATERIALS	SPECIFICATION:FINISH/COLOR	QTY.
1	HOUSING	NYLON66.UL94V-0	BEIGE	1



3D



- 1.NOTES:
1.1 ALL MATERIAL MUST BE COMPLY WITH Rohs.
1.2 MATERIAL: NYLON66
2.PRODUCT PERFORMANCE:
2.1 RATED VOLTAGE(MAX.):50V AC/DC
2.2 RATED CURRENT(MAX.):1.0A AC/DC
2.3 DIELECTRIC STRENGTH:500V AC FOR 1 MINUTE
BETWEEN ADJACENT TERMINAL, NO BREAKDOWN
2.4 INSULATION RESISTANCE:500 MEGOHMS MIN. 500V
DC FOR 1 MINUTE BETWEEN ADJACENT TERMINAL
2.5 CONTACT RESISTANCE:20 MILLIOHM MAX.
2.6 OPERATING TEMPERATURE:-25°C to +85C
3.PART NO.

30001-06D0XX-A200X

001: WATER CODE
002: 2PIN

PIN	Glowing wire specification 耐灼热丝规格	DIM A	DIM B	DIM C
2	30001-06D002-A2001	1.50	3.40	4.50
3	30001-06D003-A2001	3.00	4.90	6.00
4	30001-06D004-A2001	4.50	6.40	7.50
5	30001-06D005-A2001	6.00	7.90	9.00
6	30001-06D006-A2001	7.50	9.40	10.50
7	30001-06D007-A2001	9.00	10.90	12.00
8	30001-06D008-A2001	10.50	12.40	13.50
9	30001-06D009-A2001	12.00	13.90	15.00
10	30001-06D010-A2001	13.50	15.40	16.50
11	30001-06D011-A2001	15.00	16.90	18.00
12	30001-06D012-A2003	16.50	18.40	19.50
13	30001-06D013-A2001	18.00	19.90	21.00
14	30001-06D014-A2002	19.50	21.40	22.50
15		21.00	22.90	24.00
16		22.50	24.40	25.50

CHIN-BAN
Electronic Technology

5.0				DRAWING:	GENERAL TOLERANCE		CHIN-BAN Electronic Technology	
4.0				ShunMingWen	.X:=±0.30	.X*:=±2°		
3.0	22.01.04	新增12PIN规格	ShunMingWen	CHECKED:	.XX:=±0.20	.XX*:=±1°	DESCRIPTION: PH1.5mm WAFER WIRE-HOUSING	
2.0	21.11.10	新增13/14PIN规格	ShunMingWen	Tianhai	.XXX:=±0.10	.XXX*:=±0.5°		
1.0	21.05.27	NEW	ShunMingWen	APPROVAL:	UNIT: MM	PROJECTION:	PART NO: 30001-06D0XX-A200X REV: 3.0	
NO.	DATE	DESCRIPTION	DRAWING	Cykin	SCALE: N/A			
					SHEET: 1/1		DRAWING NO: UK0499	SIZE: A4