




REV.	REVISION DESCRIPTION	DATE	APPD

NOTES

Used in DL20034-Y Series Housing.
Accepts AWG #28~22 Wire Range.
0.08~ 0.33 mm² .
Insulation O.D.=0.8~1.5 mm.
Material : Phosphor Bronze .
Finish: Tin plated.
Thickness: 0.15 mm.
Plug-in force: Loose fit.

ORDERING INFORMATION

DL 20034 - T - X - X - X - X
1 2 3 4 5 6

1. PART NO.
2. TERMINAL CODE
3. MATERIAL TYPE: 1: PHOSPHOR BRONZE 2: BRASS 3: IRON
4: STAINLESS STEEL 5: OTHER
4. TECHNICS: 0: UNPLATED 1: FIRST PLATING 2: POST PLATING
3: OTHER
5. FINISH: 1: TIN-PLATED 2:MATTE PLATED 3:NICKEL PLATED
4:PICKLING 5: SILVER PLATED 6:GOLD PLATED
7: GALVANIZED 8:OTHER
6. SERIAL NUMBER: 00.01.02.....

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO ., LTD			
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME:		TITLE:	
.XX: ± 0.15	.X° : ± 2.0°	DL20034-H-T (PAD-H-T)		2.00 mm Pitch Crimp Terminal	
.XXX: ± 0.01	.XX° : ± 1.0°	DR:Chen Quan Long	DATE:20/01/26	PART NO:	
FINISH:		CHKD: Wu Hui	DATE:20/01/26	DL20034-T-X-X-X-XX	
DRAWING NO:		APPD:Ren An De	DATE:20/01/26	SCALE: N/A	PAGE: 1/1
GC-DL20034-T-X-X-X-XX				UNITS: mm	REV.: A

TYPE	Dimension mm				适用线规 AWG#
	A1	B1	A2	B2	
PAD-H-T	2.2	2.7	1.8	1.4	24-22
PAD-H-T-D	2.2	2.4	1.6	1.4	28-24