




RoHS

| NO. | COMPONENTS | MATERIALS       | SPECIFICATION:FINISH/COLOR | QTY. |
|-----|------------|-----------------|----------------------------|------|
| 1   | HOUSING    | Nylon66 UL94V-0 | WHITE                      | 1    |

NOTE(UNLESS OTHERWISE SPECIFIED):  
1. ALL MATERIAL MUST BE COMPLY WITH ROHS.  
2. PRODUCT PERFORMANCE:  
2.1 RATED VOLTAGE(MAX.):50V AC/DC  
2.2 RATED CURRENT(MAX.):1.0A AC/DC  
2.3 DIELECTRIC STRENGTH:500V AC/MINUTE  
2.4 INSULATION RESISTANCE:100 MΩ MIN.  
2.5 CONTACT RESISTANCE:30 mΩ MAX.  
2.6 OPERATING TEMPERATURE:-25°C TO +85°C  
3.APPLICABLE WIRE: CONDUCTOR SIZE/ AWG #32 TO #28  
INSULATION O.D./ 0.5 TO 0.9mm  
4.PART NO. :30001-C28 0XX -A4001

SUCH AS 3PIN:003



| POLES | DIM A | DIM B | DIM C |
|-------|-------|-------|-------|
| 2     | 1.25  | 3.05  | 4.15  |
| 3     | 2.50  | 4.30  | 5.40  |
| 4     | 3.75  | 5.55  | 6.65  |
| 5     | 5.00  | 6.80  | 7.90  |
| 6     | 6.25  | 8.05  | 9.15  |
| 7     | 7.50  | 9.30  | 10.40 |
| 8     | 8.75  | 10.55 | 11.65 |
| 9     | 10.00 | 11.80 | 12.90 |
| 10    | 11.25 | 13.05 | 14.15 |
| 11    | 12.50 | 14.30 | 15.40 |
| 12    | 13.75 | 15.55 | 16.65 |
| 13    | 15.00 | 16.80 | 17.90 |
| 14    | 16.25 | 18.05 | 19.15 |
| 15    | 17.50 | 19.30 | 20.40 |

|      |          |                       |             |
|------|----------|-----------------------|-------------|
| 5.0  |          |                       |             |
| 4.0  | 22.01.13 | Modify product Number | ShunMingWen |
| 3.0  | 21.08.20 | NEW PART NO.          | LWJ         |
| 2.0  | 20.07.03 | Additional sizes      | Tian hai    |
| 1.0  | 17.11.07 | NEW                   | Tian hai    |
| REV. | DATE     | DESCRIPTION           | DRAWING     |

|             |                           |
|-------------|---------------------------|
| DRAWING:    | GENERAL TOLERANCE         |
| ShunMingWen | .X:=±0.30 .X*: =±2°       |
| CHECKED:    | .XX:=±0.20 .XX*: =±1°     |
|             | .XXX:=±0.10 .XXX*: =±0.5° |
| UNIT: MM    | PROJECTION:               |
| SCALE: 1:1  |                           |
| SHEET: 1/1  |                           |

**CHIN-BAN**  
Electronic Technology

|              |                           |
|--------------|---------------------------|
| DESCRIPTION: | 1.25mm WAFER WIRE-HOUSING |
| PART NO:     | 30001-C280XX-A4001        |
| REV:         | 4.0                       |
| DRAWING NO:  | UK0362                    |
| SIZE:        | A4                        |