






RoHS2.0+REACH

NO.	COMPONENTS	MATERIALS	SPECIFICATION:FINISH/COLOR	QTY.
1	HOUSING	PBT UL94V-0	BLACK	1



- NOTE(UNLESS OTHERWISE SPECIFIED):
1. ALL MATERIAL MUST BE COMPLY WITH ROHS+REACH.
 2. PRODUCT PERFORMANCE:
 - 2.1 RATED VOLTAGE(MAX.):250V AC/DC
 - 2.2 RATED CURRENT(MAX.):7.0A AC/DC (24AWG)
 - 2.3 DIELECTRIC STRENGTH:1500V AC/MINUTE
 - 2.4 INSULATION RESISTANCE:1000 MΩ MIN.
 - 2.5 CONTACT RESISTANCE:10 mΩ MAX.
 - 2.6 OPERATING TEMPERATURE:-55°C TO +105°C
 - 3.APPLICABLE WIRE: CONDUCTOR SIZE/ AWG #24 TO #28
INSULATION O.D./ 0.8 TO 1.4mm
 - 4.PART NO. : 3GY01- R49006-A2001

WATER CODE
006:6PIN



DRAWING:	GENERAL TOLERANCE	
ShunMingWen	UNIT: MM	PROJECTION:
CHECKED:		
TianHai		
APPROVAL:		
Cykin	SCALE: 1:1	
	SHEET: 1/1	

CHIN-BAN
Electronic Technology

2.0			
1.0	09/25.24	NEW	ShunMingWen
NO.	DATE	DESCRIPTION	DRAWING

DESCRIPTION: 2*3PIN INLINE HOUSING-DOUBLE(3.81mm PITCH)	
PART NO: 3GY01-R49006-A2001	REV: 1.0
OLD CODE:	
DRAWING NO: UK0685	SIZE: A4