









RoHS+REACH

NO.	COMPONENTS	MATERIALS	SPECIFICATION:FINISH/COLOR	QTY.
1	HOUSING	LCP-E471i UL94V-0	WHITE	1
2	COVER	LCP-E471i UL94V-0	WHITE	1
3	PIN	PURPLE COPPER T2(C1100)	SQ1.14 TIN	6
4	PIN	BRASS H65	SQ0.50 TIN	4



NOTE(UNLESS OTHERWISE SPECIFIED):
1. ALL MATERIAL MUST BE COMPLY WITH ROHS+REACH
2. PRODUCT PERFORMANCE:
2.1 RATED VOLTAGE(MAX.):125V AC/DC
2.2 RATED CURRENT(MAX.):2.0A(Pitch:2.0) AC/DC
RATED CURRENT(MAX.):9.0A(Pitch:4.2) AC/DC
2.3 DIELECTRIC STRENGTH:1000V AC/MINUTE
2.4 INSULATION RESISTANCE:1000 MΩ MIN.
2.5 CONTACT RESISTANCE:20 mΩ MAX.
2.6 OPERATING TEMPERATURE:-25°C TO +85°C



P.C.B LAYOUT TOL:±0.05

5.0			
4.0			
3.0			
2.0			
1.0			
REV.	DATE	DESCRIPTION	DRAWING

DRAWING:	GENERAL TOLERANCE .X:=±0.30 .X':=±2° .XX:=±0.20 .XX':=±1° .XXX:=±0.10 .XXX':=±0.5°	
CHECKED:	UNIT: MM	PROJECTION:
APPROVAL:	SCALE: 1:1	
	SHEET: 1/1	

CHIN-BAN
Electronic Technology

DESCRIPTION: 4.20+2.00MM WIRE TO BOARD DIP180°	
PART NO: WB4200DS-10T7-P5A	REV: 1.0
DRAWING NO:	SIZE: A4