




ROHS

▲ Non-tooled parts
NO.OF POSITIONS DIM LIST:

CONTACTS	DIMENSIONS	
	A	B
1	/	2.54
2	2.54	5.08
3	5.08	7.62
4	7.62	10.16
5	10.16	12.70
6	12.70	15.24
7	15.24	17.78
8	17.78	20.32
9	20.32	22.86
10	22.86	25.40
11	25.40	27.94
12	27.94	30.48
13	30.48	33.02
14	33.02	35.56
15	35.56	38.10
16	38.10	40.64
17	40.64	43.18
18	43.18	45.72
19	45.72	48.26
20	48.26	50.80
21	50.80	53.34
22	53.34	55.88
23	55.88	58.42
24	58.42	60.96
25	60.96	63.50
26	63.50	66.04
27	66.04	68.58
28	68.58	71.12
29	71.12	73.66
30	73.66	76.20
31	76.20	78.74
32	78.74	81.28
33	81.28	83.82
34	83.82	86.36
35	86.36	88.90
36	88.90	91.44
37	91.44	93.98
38	93.98	96.52
39	96.52	99.06
40	99.06	101.60

Note:

- Material:
 - Housing: PBT / PA6T .UL94V-0;
Color: Black
 - Contact Material:Brass
- Electrical specifications
 - Rated current and voltage
3A 250V AC(r.m.s)
 - Dielectric Withstanding Voltage
600V AC for one minute
 - Contact Resistance
20mΩ Max
 - Insulation Resistance
1000MΩ Min
 - Operation Temperature
-40°C ~ +105°C

Pin Header
Pitch:6=2.54mm
Plastic Height:
E=2.54mm
NO of Contacts:
1 to 40
Series No: C

P 6 E XX C - 354430 B X P

Packing Options: P=PE

Contact Plating : 1: G/F 2:3u" 3:5u" 5:15u"
7:tin all Over
8:1u" Gold Flash Area/Tin on Tail

Insulator Material: A:PBT B:PA6T

Dimension C/D/E

DRAWING:
Hu yatao

CHECKED:
Tony

APPROVAL:
Yang jie

GENERAL TOLERANCE


.X:=±0.30 .X*:=±2°
.XX:=±0.20 .XX*:=±1°
.XXX:=±0.10 .XXX*:=±0.5°

UNIT: MM

SCALE: N/A

SHEET: 1/1

PROJECTION:



CHIN-BAN
electronics (H.K.) co., ltd

DESCRIPTION:

2.54mm Pitch Pin Header Single Row DIP90°

PART NO: P6EXXC-354430-BXP

REV: 1.0

CUSTOMER NO:

SIZE: A4