

RoHS2.0+REACH

NO.	COMPONENTS	MATERIALS	SPECIFICATION:FINISH/COLOR	QTY.
1	HOUSING	PBT UL94V-0	BLACK	1

NOTE(UNLESS OTHERWISE SPECIFIED):

1. ALL MATERIAL MUST BE COMPLY WITH ROHS+REACH.

2. PRODUCT PERFORMANCE:

2.1 RATED VOLTAGE(MAX.):250V AC/DC

2.2 RATED CURRENT(MAX.):7.0A AC/DC(24AWG)

2.3 DIELECTRIC STRENGTH:1500V AC/MINUTE

2.4 INSULATION RESISTANCE:1000 MΩ MIN.

2.5 CONTACT RESISTANCE:10 mΩ MAX.

2.6 OPERATING TEMPERATURE:-55°C TO +105°C







3.APPLICABLE WIRE: CONDUCTOR SIZE/ AWG #24 TO #28

INSULATION O.D./ 0.8 TO 1.4mm


4.PART NO. : 3GY01- P19004-A200X

WATER CODE


004:4PIN




P/N: 3GY01-P19004-A2001 (X KEYING)



P/N: 3GY01-P19004-A2002 (Y KEYING)



3D VIEW FOR X KEYING



3D VIEW FOR Y KEYING

DRAWING:
ShunMingWen

CHECKED:
TianHai

APPROVAL:
Cykin

GENERAL TOLERANCE

.X:=±0.30

.XX:=±0.20

.XXX:=±0.10

.X°:=±2°

.XX°:=±1°


.XXX°:=±0.5°

UNIT: MM

SCALE: 1:1

SHEET: 1/1

PROJECTION:



CHIN-BAN
Electronic Technology

DESCRIPTION: 4PIN FEMALE HOUSING(3.81mm PITCH)

PART NO: SEE NOTES

OLD CODE:

DRAWING NO: UK0628

REV: 1.0

SIZE: A4

2.0			
1.0	09/25.24	NEW	ShunMingWen
NO.	DATE	DESCRIPTION	DRAWING