

RoHS2.0



NO.	COMPONENTS	MATERIALS	SPECIFICATION:FINISH/COLOR	QTY.
1	HOUSING	Nylon66 UL94-V0	BEIGE/BLACK	1

NOTE(UNLESS OTHERWISE SPECIFIED):

1. ALL MATERIAL MUST BE COMPLY WITH ROHS2.0

2. PRODUCT PERFORMANCE:

2.1 RATED VOLTAGE(MAX.):50V AC/DC

2.2. RATED CURRENT(MAX.):1.0A AC/DC

2.3 DIELECTRIC STRENGTH:100V AC/MINUTE

2.4 INSULATION RESISTANCE:100 MΩ MIN.



2.5 CONTACT RESISTANCE:30 mΩ MAX.

2.6 OPERATING TEMPERATURE:-25°C TO +85°C




3.APPLICABLE WIRE: AWG #28 TO #32

4.PART NO. :30001-06 X XXX-A20XX

CODE
PIN: 008: 8PIN 3.0 5.0
COLOR 8/D:BEIGE 9:BLACK
06:PA66



3D VIEW



CODE(BLACK)	CODE(BEIGE)	POLES	DIM A	DIM B	DIM C
	30001-06D006-A2005	2*3P	2.00	7.70	8.70
	30001-068008-A2006	2*4P	3.00	8.70	9.70
30001-069010-A2001	30001-06D010-A2005	2*5P	4.00	9.70	10.70
30001-069012-A2001	30001-068012-A2003	2*6P	5.00	10.70	11.70
	30001-06D014-A2003	2*7P	6.00	11.70	12.70
30001-069016-A2001	30001-068016-A2002	2*8P	7.00	12.70	13.70
	30001-06D018-A2001	2*9P	8.00	13.70	14.70
	30001-068020-A2003	2*10P	9.00	14.70	15.70
	30001-06D022-A2002	2*11P	10.00	15.70	16.70
	30001-06D024-A2001	2*12P	11.00	16.70	17.70
	30001-06D026-A2001	2*13P	12.00	17.70	18.70
		2*15P	14.00	19.70	20.70
		2*20P	19.00	24.70	25.70
		2*25P	24.00	29.70	30.70

CHIN-BAN
Electronic Technology

5.0	23.10.10	Add product specifications	ZQH	DRAWING:	GENERAL TOLERANCE .X:=±0.30 .X*:=±2* .XX:=±0.20 .XX*:=±1* .XXX:=±0.10 .XXX*:=±0.5*	
4.0	22.10.12	Newly added product specifications	ZQH	LWJ		
3.0	22.06.24	1.Revise the specification of product number 2.Update the drawing frame	ZQH	CHECKED:	UNIT: MM	PROJECTION:
2.0	21.10.29	New specification number	ZQH	Tianhai	SCALE: 1:1	
1.0	21.05.07	NEW	LWJ	APPROVAL:	SHEET: 1/1	
REV.	DATE	DESCRIPTION	DRAWING	Joey		

DESCRIPTION: PH1.0 DOUBLE-BREASTED BUCKLE-HOUSING	
PART NO: 30001-06XXXX-A20XX	REV: 5.0
DRAWING NO: UK0480	SIZE: A4